



Recommend of PC Board Holes
Tolerance : ±0.05(Top view)

主要技术特性要求:

- 使用条件:
环境温度: -25~70°
相对湿度: 95% (40°)
- 额定负荷: DC20V 15A
- 接触电阻: ≤30mΩ 寿命测试后: ≤60mΩ
- 绝缘电阻: ≥100MΩ
- 耐压: AC500V (50Hz) 1min
- 插拔力: 3-20N 寿命测试后: 3-20N
- 寿命: 5000次
- 焊接耐热: 红外回流焊
- 包装: 盘装

				TOLERANCE UNLESS SPECIFIED							
				UP TO 5mm: ±0.1	ANGULAR	1					
				ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD
6	中心针	BRASS	1	Au/Sn-PLATED	TITLE: DC JACK		UNIT : MM	ROHS	DWN		
5	正极针	CORSON ALLOY	1	Au-PLATED	MODEL: DC-7406-04		SCALE: 1:1	COMPLIANT	CHK'D		
4	负极长针	CORSON ALLOY	1	Au-PLATED	 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司		APPD				
3	负极短针	CORSON ALLOY	1	Au-PLATED			PRO.AGL: 		REV :A0		
2	屏蔽外壳	BRASS	1	Ni-PLATED							
1	主体	PA10T	1	BLACK							
NO.	PART NAME	MATERIAL	QTY	FINISHING							