










HAOYU



3D VIEW




SCHEMATIC



P. C. B LAYOUT
TOP VIEW

(ø3.50mm 5 POLE PLUG DETAIL DRAWING)

				TOLERANCE UNLESS SPECIFIED							
7				UP TO 5mm: ±0.1	ANGULAR						
6				ABOVE 5mm: ±0.2	±1°						
5	HOUSING	PA9T	1	BLACK		NO	DATE	REVISIONS		BY	APPD
4	TERMINAL 4#	SUS	1	Ni/Ag-PLATED	TITLE: PHONE JACK		UNIT : MM	ROHS	DWN		
3	TERMINAL 3#	SUS	1	Ni/Ag-PLATED	MODEL: PJ-3505A		SCALE: 1:1	COMPLIANT	CHK'D		
2	TERMINAL 2#	PBS	3	Ni/Ag-PLATED	 HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司				APPD		
1	TERMINAL 1#	PBS	1	Ni/Ag-PLATED							PRO.AGL:
NO.	PART	NAME	MATERIAL	QTY	FINISHING						