## **The Outdoor Board**

Outdoor Wall Mount Panel Cellular Antenna





BT512365

## The Board from Bolton: So easy to install, you'll be up boosting in minutes.

- Directional broadcast panel antenna for your cellular signal boosting system
- The Board works with all 50 Ohm signal boosters
- Easy installation your DIY skills will make swift work of it
- Up to +8 dBi gain



ELECTRICAL STUFF			Product Specifications may change without prior notice.	
Item No.		BT512365		
Frequency Range		MHz	698-960	1710-2700
Gain		dBi	6.5	8
Polarization		Vertical		
Beam width	Horizontal	deg	80	65
	Vertical		73	60
VSWR			≤1.8	
Front-To-Back Ratio		dB	>12	>18
PIM, 3rd Order, 2 x 2 W		dBc	≤-153	
Input Power, maximum		watt	50	
Impedance		ohm	50	

MECHANICAL STUFF				
Connector Type	N-Female			
Dimensions, HxWxD	mm, in	165 x 155 x 50, 6.50 X 6.10 X 2.00		
Weight, without Mounting Kit	kg, lbs	0.25, 0.55		
Radome Material and Color		ABS, White, RAL7035		
Mounting Kit		On-wall		
Operational Temperature	oC, oF	-55 to +60, -67 to 140		
Ingression Protection Rating		IP65		
Cable Length	cm, in	30, 11.81		
Coax Type		RG141		











VERTICAL













www.boltontechnical.com

**5010 Wright Road, Suite 115** Stafford, TX, 77477

