The Cowboy

Ceiling Mount Dome Antenna





BT512600

The ideal ceiling mount antenna for transmitting & receiving in 360-degree view

- Built for the USA band ranges covering 698 MHz to 2700 MHz
- Wideband omnidirectional indoor antenna for use with signal boosting systems
- Low return loss and stable performance in a compact, lightweight design
- Up to +5 dBi gain, designed for 50 Ohm Systems
- Easy to install

| ELECTRICAL STUFF | | | Product Specifications may change without prior notice. | |
|-------------------------|------------|----------|---|-----------|
| Item No. | | BT512600 | | |
| Frequency Range | | MHz | 698-960 | 1710-2700 |
| Gain | | dBi | 2 | 5 |
| Polarization | | | Vertical | |
| Beam width | Horizontal | deg | 360 | |
| | Vertical | | 60 | 35 |
| VSWR | | | ≤1.8 | ≤1.5 |
| PIM, 3rd Order, 2 x 20W | | dBc | ≤-153 | |
| Un-Roundness | | dB | ±2 | |
| Maximum Input Power | | watt | 50 | |
| Impedance | | ohm | 50 | |

| MECHANICAL STUFF | | | | | |
|------------------------------|----------|-------------------------------------|--|--|--|
| Connector Type | N-Female | | | | |
| Size | mm, in | 203 x 98, 8.00 x 3.86 | | | |
| Packing Size | mm, in | 210 x 210 x 110, 8.25 x 8.25 x 4.33 | | | |
| Antenna Weight | kg, lb | 40, 0.88 | | | |
| Packing Weight | kg, lb | 45, 1.00 | | | |
| Operational Temperature | °C, °F | -40 to 55, -40 to 131 | | | |
| Radome Material and Color | | ABS, White, RAL 7035 / Pantone 421 | | | |
| Ingression Protection Rating | | IP65 | | | |
| Cable Length | cm, in | 34, 13.38 | | | |
| Coax Type | | RG141 | | | |



RADIATION PATTERNS

HORIZONTAL

900 MHz

1710 MHz

2500 MHz

VERTICAL

900 MHz







www.boltontechnical.com