

P/N LEGEND



A1253 H-XP

① ② ③

① Series No.
 ② Connector type: H=Housing
 ③ No. of circuits

SPECIFICATIONS
 Current Rating: 1A AC,DC
 Voltage Rating: 150V AC,DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 30mΩ Max.
 Insulation Resistance: 500MΩ Min.
 Withstanding Voltage: 500V AC/minute
 Material: Nylon 66,UL94V-0
 Pantone color: 7529C

Circuit No.	Dimensions		
	A	B	C
02P	1.25	4.25	2.75
03P	2.50	5.50	4.00
04P	3.75	6.75	5.25
05P	5.00	8.00	6.50
06P	6.25	9.25	7.75
07P	7.50	10.50	9.00
08P	8.75	11.75	10.25
09P	10.00	13.00	11.50
10P	11.25	14.25	12.75
11P	12.50	15.50	14.00
12P	13.75	16.75	15.25
13P	15.00	18.00	16.50
14P	16.25	19.25	17.75
15P	17.50	20.50	19.00
20P	23.75	26.75	25.25
21P	25.00	28.00	26.50
25P	30.00	33.00	31.50
30P	36.25	39.25	37.75

 燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.			
UNIT	SCALE	SHEET	TITLE:
mm	1 : 1	1 of 1	
DRAWN BY	APPROVED BY		1.25mm PITCH HOUSING ULTRA LOW PROFILE
董正一 2001.02.01	董正一 2001.02.01		
GENERAL TOLERANCE			DRAW NO. : A1253H-XP
X. X±0.25	ANGLE±		
X. XX±0.15			REV. B3
X. XXX±0.05			
B3	EN1103220076	2011.03.22	陳敏
REV.	DESCRIPTION	DATE	NAME