

RoHS compliant  
by exemption

Crimping tools for outer conductor  
see document 2195600660  
Cable RG179BU, RG187AU

1731120466	FMS002S101	101
1727040131	FMS002S102	102
1731121067	FMS002S202	202
Material Number	FCT Part Number	Material + Finish See extra sheet


**Crimping tools:**  
Crimping of inner conductor:

Hand tool: 1731121730  
Locator: 1731121738

Pneumatic crimp tool: WA22  
Locator: 1731121738

Cable:  
AWG 24 / SEL. 5  
AWG 26 / SEL. 5  
AWG 28 / SEL. 4  
AWG 30 / SEL. 3

**Cable trimming dimensions**



UNLESS OTHERWISE SPECIFIED DIMENSIONS FOR REFERENCE ONLY				REPLACEMENT FOR DOCUMENT NUMBER: FMS002S						
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
FUNCTIONAL SYMBOLS	DIMENSION UNITS	SCALE	CURRENT REV DESC:							
$\frac{E}{A} = 0$	mm	5:1	EC NO: 710219 DRWN: VLOKESHA 2021/04/19 CHK'D: MTEUBEL 2022/06/22 APPR: MTEUBEL 2022/06/22 INITIAL REVISION: DRWN: VLOKESHA 2021/04/19 APPR: MTEUBEL 2022/06/22							
$\frac{E}{E} = 0$	GENERAL TOLERANCES (UNLESS SPECIFIED)									
$\frac{E}{P} = 0$	ANGULAR TOL ± °									
DIVISIONAL SYMBOLS	4 PLACES	±								
	3 PLACES	±	DOCUMENT NUMBER: 1731120466 DOC TYPE: PSD DOC PART: 000 REVISION: A							
	2 PLACES	±								
	1 PLACE	±								
	0 PLACES	±	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		FIRST ANGLE PROJECTION	DRAWING: A4-SIZE	SERIES: 173112	MATERIAL NUMBER: SEE TABLE	CUSTOMER: GENERAL MARKET	SHEET NUMBER: 1 OF 1