# **SHROUDED HEADERS**



(2.00 mm) .0787" PITCH • TSH/TMMS SERIES

#### **TSH** Mates:

CLT, SQT, SQW, ESQT, TLE, SMM, MMS, PTF

### **TMMS** Mates:

SQT, SQW, ESQT

## **SPECIFICATIONS**

**Insulator Material:** Black Liquid Crystal Polymer **Terminal Material:** Phosphor Bronze Plating: Sn or Au over 50 µ" (1.27 µm) Ni Operating Temp Range: -55 °C to +105 °C with Tin; -55 °C to +125 °C with Gold

### **PROCESSING**

### Lead-Free Solderable:

Yes SMT Lead Coplanarity (TSH):

(0.15 mm) .006" max\* \*(.004" stencil solution may be available; contact IPG@samtec.com)

NO. PINS **PER ROW** 

05, 10, 15, 20, 25, 30, 35, 40, 45 (40 & 45 = -D & -RA only) (Standard sizes)

(4.00)

(No. of positions + 2) x (2.00) .0787

## on post, Matte Tin on tail

**PLATING** 

**OPTION** 

–F

Gold flash

**-L** = 10 μ" (0.25 μm) Gold on post, Matte Tin on tail

#### -T = Matte Tin

#### **ROW OPTION**

-D = Vertical Through-hole

#### -DV = Vertical Surface

Mount

## -RA = Right-angle Through-hole

-DH = Horizontal Surface Mount

#### OTHER OPTION

#### -LC = Locking Clip (-DV only) (Not available with -A) (Manual placement required)

= Alignment Pin (-DV only) (Not available with -LC)

#### -SL = Solder Locks (-DH only)

-K = (4.50 mm) .177" DIA Polyimide Film Pick & Place Pad (-DH only) (Not available with 15 - 30 positions)

## -TR

= Tape & Reel

## -FR


= Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks)

# (2.46) -D

.207







# **TMMS**

NO. PINS PER ROW

**PLATING OPTION** 

# OPTION

## 05, 10, 15, 20, 30, 40, 50


= Gold flash on post, Matte Tin on tail


 $\begin{array}{c} \textbf{-L} \\ = 10 \; \mu \text{" (0.25 } \mu \text{m)} \\ \text{Gold on post,} \\ \text{Matte Tin on tail} \end{array}$ 


### -RA = Right-angle

#### ALSO AVAILABLE MOQ Required

Other plating







#### Note:

Some lengths, styles and options are non-standard, non-returnable.