

6

5

4

3





2

1

APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	01/17/07	
A		UPDATED SPECIFICATIONS	7/28/09	
B		REVISED SHAPE	3/23/11	
C		UPDATE DRAWING	1/19/19	AYTY



**SPECIFICATIONS:**

Material:  
Insulator: Nylon 66, rated UL 94V-0  
Insulator color: Natural

**Electrical:**

Current rating: 1A AC/DC  
Contact resistance: 20 mohms max  
Insulation resistance: 500 Mohms min  
Dielectric withstanding voltage: 500 VAC for 1 minute

**Temperature Rating:**

-25°C to +85°C

Environmental:

Lead free, RoHS compliant.



Positions: 02 thru 15

A = .059 [1.50] X No. of Spaces.

B = .059 [1.50] X No. of Spaces + .118 [3.00].

C = .059 [1.50] X No. of Spaces + .075 [1.90].

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010		<b>ADAM</b> <b>TECH</b> <b>INTERCONNECTS</b>		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS		DATE		TITLE	
DRAWN	BW	01/17/07		ZH 1.50mm HOUSING	
CHECKED		SIZE	PART NO.	REV.	
APPROVED		X	15CH-A-XX	B	
REF: S00124T		SCALE: NTS	SHEET 1 OF 1		

6

5

4

3

2

1