



Specifications  
 Current Rating:3.0A AC/DC  
 Voltage Rating:250V AC/DC  
 Contact Resistance:20m ohm. Max  
 Insulation Resistance:1000M ohm. Min  
 Withstanding Voltage:600V AC For one minute  
 Operating Temperature Range : -40°C to +105°C

Material:  
 Plastic:Nylon 6T (UL94V-0)  
 Standard Color:Black  
 Contact:Copper Alloy  
 Plating:Gold Plated




Notes:  
 60P · 64P With Three Key  
 All Other Pin With One Key


Circuits	Dim A	Dim B	Circuits	Dim A	Dim B
6	27.12	5.08	26	52.52	30.48
8	29.66	7.62	30	57.60	35.56
10	32.20	10.16	34	62.68	40.64
12	34.74	12.70	40	70.30	48.26
14	37.28	15.24	50	83.00	60.96
16	39.82	17.78	60	95.70	73.66
20	44.90	22.86	64	100.78	78.74
24	49.98	27.94			



MATING PART  
 3030-XX-0103-00



MATING PART  
 3030-XX-0104-00



RoHS Compliant

REV	DATE	FILE	BY	DRAWN: Romina Wu	GENERAL TOLERANCE: .X=±0.20 .XX=±0.15	<h1 style="color: red; text-align: center;">CnC Tech</h1> <p style="text-align: center;">Industrial Cable and Connector Technology</p>	DESCRIPTION: 2.54mm Shrouded Header With Ejector SMD Type	SIZE A4
				CHECKED: Jerry Chen	UNIT: MM			
				APPROVAL: Rory Chen	SCALE:1:1	PART NO: 3010-XX-003-13-00		
	05-FEB-2020				SHEET: 1 / 1			
					PROJECTION:			