


Specifications:
 Current Rating: 3.0A AC,DC
 Voltage Rating: 250V AC,DC
 Contact Resistance: 10mohm Max
 Insulation Resistance: 1000Mohm Min.
 Withstanding Voltage: 1000V AC/minute
 Operating Temperature Range: -25°C ~ +85°C

Material And Finish:
 Insulator: Nylon 66 (UL94V-0)
 Insulator Color: White
 Contact: Brass
 Plated: Tin Plated

Dimension:

POS.	Dim.A	Dim.B	POS.	Dim.A	Dim.B
2	2.50	7.50	9	20.00	25.00
3	5.00	10.00	10	22.50	27.50
4	7.50	12.50	11	25.00	30.00
5	10.00	15.00	12	27.50	32.50
6	12.50	17.50			
7	15.00	20.00			
8	17.50	22.50			



RoHS Compliant

REV	DATE	FILE	BY
	17-Nov-2020		

DRAWN:	GENERAL TOLERANCE: .X = ±0.20 .XX = ±0.15
CHECKED:	UNIT: MM SCALE: 1:1
APPROVAL:	SHEET: 1 / 1
	PROJECTION:

CnC Tech Industrial Cable and Connector Technology	
DESCRIPTION: Wire-To Board Wafer .25mm, Straight, Tin Plated, J Series	SIZE: A4
PART NO: 51025-XX-0100-01	