44423232	DATA SHEET	
Valid from: 17.09.2018	EPIC® MH 0	W LA

## Description

- Dummy module as a placeholder for future expansion
- EPIC<sup>®</sup> MH system is pluggable with the market standars
- The mix of different functions in one plug guarantees high flexibility



## **General characteristics**

Number of contacts

Material Polyamide, glass fibre-reinforced

Inflammability class acc. with UL 94

Temperatue range -40° C to +125° C

Epic<sup>®</sup> MH 6 multi-frame Epic<sup>®</sup> MH 10 multi-frame Epic<sup>®</sup> MH 16 multi-frame

Suitable frame


Epic® MH 24 multi-frame

# Standards/Approvals

Fire protection on railway vehicles according EN 45545-2

requirement sets R22 and R23 hazard level HL1, HL2 and HL3

## **Drawings**



EPIC ® MH 0 44423232



## Note

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP	Document: DB44423232EN	Dage 1 of 1
Released: IVSE1/PDP	Version: 01	Page 1 of 1