







1 2 3 4 5



Specifications:
Current Rating: 1A AC,DC
Voltage Rating: 50V AC,DC
Contact Resistance: 20m ohm.Max
Insulation Resistance: 1,000M ohm.Min
Withstanding Voltage: 500V AC/Minute
Operating Temperature Range: -40°C ~ +105°C

Material:
Insulator: PBT(UL94V-0)
Insulator Color: Black
Contact: Phosphor Bronze
Finish: Gold Plated Over Nickel

Dimension:

Pin	Dim.A	Dim.B	Dim.C
6	2.54	8.00	11.80
8	3.81	9.27	13.07
10	5.08	10.54	14.34
12	6.35	11.81	15.61
14	7.62	13.08	16.88
16	8.89	14.35	18.15
18	10.16	15.62	19.42
20	11.43	16.89	20.69
24	13.97	19.43	23.23
26	15.24	20.70	24.50
28	16.51	21.97	25.77
30	17.78	23.24	27.04
34	20.32	25.78	29.58
40	24.13	29.59	33.39
44	26.67	32.13	35.93
50	30.48	35.94	39.74

RoHS Compliant

				DRAWN: Jerry	GENERAL TOLERANCE: .X=±0.20 .XX=±0.15	CnC Tech Industrial Cable and Connector Technology	
				CHECKED:	UNIT: MM		DESCRIPTION: 1.27x1.27mm Flat Cable IDC Socket With Strain Relief
					SCALE:1:1	PART NO: 3230-XX-0103-00	A4
	05-FEB-2020			APPROVAL: Rory	SHEET: 1 / 2		
REV	DATE	FILE	BY		PROJECTION:		