

Replacement - Tube Guitar Output (1750 Series)



TUBE GUITAR AMPLIFIER - OUTPUT TRANSFORMERS

- Designed for drop in replacement of original tube guitar amplifier output transformers.
- Physically, parts were designed to look similar to original factory units (where possible).
- Material used & design specs. were kept as close as possible to the original part to preserve the stock "tone".
- For individual photos of each part - visit our website: www.hammondmfg.com

Part No.	Primary (Ohms)	Secondary (Ohms)	Amplifier Type	Power (Watts)	Amplifier Manufacturer	Amplifier Model Names	Equivalent To Mfg's Part Number
1750A	22,800	8	Single Ended	3.5	Fender	Reverb Driver	125A20B & 022921
1750C	7,000	3.2	Single Ended	5	Fender	Champ, Vibro-Champ, Bronco	125A35A & 022905
1750E	8,000 C.T.	8	Push-Pull	15	Fender	Princeton Reverb, Tweed Deluxe	125A10B & 022913
1750F	6,950 C.T.	8	Push-Pull	15	Fender	Blues Junior	049969
1750H	6,600 C.T.	8	Push-Pull	20	Fender	Deluxe, Deluxe Reverb	125A1A & 022640
1750J	4,000 C.T.	4	Push-Pull	35	Fender	Pro-Reverb, Tremolux, Vibrolux	125A6A & 022848
1750K	4,000 C.T.	2	Push-Pull	50	Fender	Tweed Bassman, Super Reverb	125A9A & 022855
1750L	4,200 C.T.	4	Push-Pull	50	Fender	Bassman	125A13A & 022871
1750M	4,200 C.T.	2, 4, 8	Push-Pull	50	Fender	General Replacement	125A13A & 022871
1750W	2,000 C.T.	4	Push-Pull	100	Fender	Dual Showman, Twin Reverb	125A29A & 022889
1750N	3,200 C.T.	4, 8, 16	Push-Pull	50	Marshall	JMP, JCM 800	-
1750P	126, 500, 2,000	2, 4, 8, 16	Push-Pull	50	Marshall	JCM 900	-
1750Q	7,371 C.T.	4, 8, 16	Push-Pull	50	Marshall	JTM 45	-
1750U	1,700 C.T.	4, 8, 16	Push-Pull	100	Marshall	JMP, JCM 800	-
1750X	126, 500, 2,000	2, 4, 8, 16	Push-Pull	100	Marshall	JCM900	-
1750Y	6,300 C.T.	8	Push-Pull	15	VOX	AC15	-
1750V	4,000 C.T.	8, 16	Push-Pull	30	VOX	AC30 Vintage	-
1750T	4,000 C.T.	8, 16	Push-Pull	30	VOX	AC30 Reissue	-
1750G	3,800 C.T.	4, 8, 16	Push-Pull	50	Yorkville/Traynor	General Replacement	-
1750R	2,000 C.T.	4, 8, 16	Push-Pull	100	Yorkville/Traynor	General Replacement	-

DISCLAIMER: Hammond Mfg. is not affiliated with Fender Musical Instruments Corp., Marshall Amplification, Yorkville/Traynor or VOX Amplification companies. Amplifier model names Blues Junior, Bandmaster, Bandmaster Reverb, Bassman, Bassman 100, Bronco, Champ, Vibro-Champ, Deluxe, Deluxe Reverb, Dual Showman, Princeton Reverb, Pro Reverb, Reverb Driver, Super Reverb, Tremolux, Tweed Bassman, Tweed Deluxe, Twin Reverb, Twin Super, Vibrolux & Vibrolux Reverb are all trademarks of Fender Musical Instruments Corp.



CANADA

Guelph, Ontario (519) 822-2960
St. Laurent, Quebec (514) 343-9010

USA

Cheektowaga, NY (716) 630-7030

www.hammondmfg.com



EUROPE

Basingstoke, UK 01256 812812

AUSTRALIA

Queenstown, Australia 61-8-8240-2244

Replacement - Tube Guitar Power (290 Series)



TUBE GUITAR AMPLIFIER - POWER TRANSFORMERS

- Designed for drop in replacement of original tube guitar amplifier power supply transformers.
- Physically, parts were designed to look similar to original factory units (where possible).
- For individual photos of each part - visit our website: www.hammondmfg.com

Part No.	Primary	Amplifier Manufacturer	Amplifier Model Names	Equivalent To Mfg'ers Part Number
290AX 290AEX	120VAC 60 Hz. 240VAC 50 Hz.	Fender	Champ, Vibro Champ, Princeton, Princeton Reverb, Tweed Deluxe	125P1B & 022772
290BX 290BEX	120VAC 60 Hz. 240VAC 50 Hz.	Fender	Deluxe, Deluxe Reverb	125P23D & 041316
290CX 290CEX	120VAC 60 Hz. 240VAC 50 Hz.	Fender	Vibrolux, Vibrolux Reverb, Tremolux	125P26A & 022723
290DX 290DEX	120VAC 60 Hz. 240VAC 50 Hz.	Fender	Super Reverb, Pro Reverb, Bandmaster Reverb, Tweed Bassman	125P5D & 022798
290EX 290EEX	120VAC 60 Hz. 240VAC 50 Hz.	Fender	Bassman, Concert, Pro	125P7D & 022814
290FX 290FEX	120VAC 60 Hz. 240VAC 50 Hz.	Fender	Twin Reverb, Dual Showman, Bassman 100	125P34A & 022756
290GX	120/220/240VAC 50/60 Hz.	Marshall	JCM 800, JMP - 50 Watt	-
290HX	120/220/240VAC 50/60 Hz.	Marshall	JCM 800, JMP - 100 Watt	-
290KX	120/240VAC 50/60 Hz.	Marshall	JCM 900 - 50 Watt	-
290JX	120/240VAC 50/60 Hz.	Marshall	JCM 900 - 100 Watt	-
290LX	120/240VAC 50/60 Hz.	Marshall	JTM 45	-
290PX	120/240VAC 50/60 Hz.	VOX	AC15	-
290NX	100/120/220/230/240VAC 50/60 Hz.	VOX	AC30 Vintage	-
290MX	120/240VAC 50/60 Hz.	VOX	AC30 Reissue	-

DISCLAIMER: Hammond Mfg. is not affiliated with Fender Musical Instruments Corp., Marshall Amplification, Yorkville/Traynor or VOX Amplification companies. Amplifier model names Bandmaster Reverb, Bassman, Bassman 100, Champ, Vibro Champ, Concert, Deluxe, Deluxe Reverb, Dual Showman, Princeton, Princeton Reverb, Pro, Pro Reverb, Super Reverb, Tremolux, Tweed Bassman, Tweed Deluxe, Twin Reverb, Vibrolux & Vibrolux Reverb are all trademarks of Fender Musical Instruments Corp.

Guitar Amp

EUROPE

Basingstoke, UK 01256 812812

AUSTRALIA

Queenstown, Australia 61-8-8240-2244

www.hammondmfg.com



CANADA

Guelph, Ontario (519) 822-2960
St. Laurent, Quebec (514) 343-9010

USA

Cheektowaga, NY (716) 630-7030



Replacement - Tube Guitar Chokes (194 Series)



TUBE GUITAR AMPLIFIER - POWER TRANSFORMERS

- Designed for drop in replacement of original tube guitar amplifier power supply chokes.
- Physically, parts were designed to look similar to original factory units (where possible).
- For individual photos of each part - visit our website: www.hammondmfg.com

Part No.	Inductance (Henrys)	Amplifier Manufacturer	Amplifier Model Names	Equivalent To Mfg's Part Number
194A	4	Fender	Deluxe, Deluxe Reverb, Vibrolux, Vibrolux Reverb	125C3A & 022707
194B	4	Fender	Bandmaster, Dual Showman, Pro Reverb, Twin Super	125C1A & 022699
194C	40	Marshall	JCM 800	-
194D	5	VOX	AC30 reissue	-
194E	30	VOX	AC30 vintage	-

DISCLAIMER: Hammond Mfg. is not affiliated with Fender Musical Instruments Corp., Marshall Amplification or VOX Amplification companies. Amplifier model names Bandmaster, Deluxe, Deluxe Reverb, Dual Showman, Pro Reverb, Twin Super, Vibrolux & Vibrolux Reverb are all trademarks of Fender Musical Instruments Corp.

Guitar Amp



CANADA

Guelph, Ontario (519) 822-2960
St. Laurent, Quebec (514) 343-9010

USA

Cheektowaga, NY (716) 630-7030

www.hammondmfg.com



EUROPE

Basingstoke, UK 01256 812812

AUSTRALIA

Queenstown, Australia 61-8-8240-2244