

1

2





3

4

5

6

7



### ① Dimensions

Positions	A	B	D	E
9	30.81	24.99	16.33	11.08
15	39.20	33.30	24.70	19.39
25	53.05	47.04	38.40	33.24
37	69.40	63.50	54.80	49.86

----- ADFXXA-KG-TXXB5  
 Contacts: 09, 15, 25, 37  
 With Hex Stand-Off (S) or Without Hex Stand-Off (X)

- Electrical:**
- Contact Resistance: 20mΩ Max @1A DC
  - Insulation Resistance: 1,000MΩ @500V DC
  - Dielectric Withstanding Voltage: 1,000V AC/rms 60Hz for 1 minute
- ①
- Current rating: 3 Amp
  - Voltage rating: 250V AC/rms 60Hz

## RoHS compliant

Unit: mm

Scale	Free					
TOLERANCE						
X.	±0.38					
X.X	±0.25					
X.XX	±0.13					
DIM		TOL				
X.°	±3°		① Update			
X.X°	±1°		② Drawn			
Angle	TOL	Id.	Modification	Date	Name	

Customer-No.

Name

Date

Drawn

23.05.2013

Wilson

Winnie

05.06.2013

Approved

05.06.2013

Winnie

ASSMANN WSW-No.  
ADFXXA-KG-TXXB5

Drawing-No.

ASS 5750 CO rev01

Replace

Sheet

1

2

3

4

5

6

7

SV3238