



Material and Finish

Shell: Steel, Nickel plated
 Insulator: PBT thermoplastic with glass-fiber reinforcement, UL94V-0 rated
 Color: Black

Contact Material:
 Socket - Brass

Contact Plating Options:
 Standard: gold flash on mating end, tin on termination end, nickel underplate on entire contact

15 Option: 15u" gold on mating end, tin on termination end, nickel underplate on entire contact

30 Option: 30u" gold on mating end, tin on termination end, nickel underplate on entire contact

Electrical Specifications

Rated Current: 1.5A
 Rated Voltage: 30Vac
 Insulation Resistance: more than 1000 megohms at 500V DC
 Contact Resistance: 13 milliohms max.
 Dielectric Withstanding Voltage: 1000V for 1 minute
 Operating Temperature: -55°C to +75°C

Part Number	Contact Area Plating Finish
K86X-BA-44S-KJ	Gold Flash (standard)
K86X-BA-44S-KJ15	15u" Gold (15 option)
K86X-BA-44S-KJ30	30u" Gold (30 option)

Tolerances
X.X ± 0.25
X.XX ± 0.15
Unless Stated Otherwise



REV.	DATE	DESCRIPTION	REV. BY	CHK. BY	DRAWN BY	DATE
A1	03/30/09	New Drawing	S. Vien	H. MA		
A2	9/10/14	ECO#14-028	H. MA	P. DalCanto	S. Vien	02/17/09
A3	12/31/17	ECO# 17-033	G. Serrato	C. Furumasu		
					UNITS	
					mm	

K86X-BA-44S-KJ

D-Sub, HD, Vertical, Soldercup, RoHS Compliant
 44-Pin Socket, JS, Threaded Bushings

