


Recommended PCB Layout



Material And Finish

Shell: Steel Material, Nickel Plated

Insert: PBT Thermoplastic,
Black Color, 30%
Glass Filled, UL 94V-0 Rated

Contact Material:
Plug - Brass

Contact Plating:

Standard:

Gold flash on mating end,
tin on termination end, with
entire contact nickel underplated

-15 Option:

15u" gold on mating end,
tin on termination end, with
entire contact nickel underplated

-30 Option:

30u" gold on mating end,
tin on termination end, with
entire contact nickel underplated

Electrical Specifications

Rated Current: 2A

Rated Voltage: 30V RMS

Dielectric Withstanding Voltage:
1000V (rms) AC for 1 minute

Insulation Resistance:
more than 1000 Megohm
at 500V DC

Dielectric Withstanding Voltage-
1000 VAC rms for 1 minute

Contact Resistance:
13 milliohm max.

Operating Temperature
-55°C to +105°C

Ordering Information

Part Number	Contact Area Plating Finish
K85X-BD-25P-BR	Gold Flash (standard)
K85X-BD-25P-BR15	15u" Gold (15 option)
K85X-BD-25P-BR30	30u" Gold (30 option)



Tolerances
X.X ± 0.25
X.XX ± 0.15
Unless Stated Otherwise

REV.	DATE	DESCRIPTION	REV. BY	CHK. BY	DRAWN BY	DATE
A1	10/13/05	New Drawing	R. Aguirre	H. MA	R. Aguirre	10/13/05
A2	1/9/08	ECO #07-052	WILL H.	H. MA		
A3	12/31/17	ECO #17-030	J. Elbanna	C. Furumasu		
					UNITS	
					mm	

K85X-BD-25P-BR

Vertical PCB Mount D-Sub ,RoHS Compliant

25 Pin Male, w/ Boardlocks

