
DESCRIPTION: HIGH DENSITY MALE - VERTICAL DIP SOLDER



Rohs COMPLIANT


THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION. DRAWN: P. JENKINS DATE: 09/12/2005

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING

orComp	SCALE: NTS	SHEET 1	OF 3	REV 20	
	DWG NO.	^{G NO.} 180-YYY-113RYY1			

DESCRIPTION: HIGH DENSITY MALE - VERTICAL DIP SOLDER





ALL CLINCH-NUTS ARE 4-40 INTERNAL THREADS


01 0.098" (BOARD SIDE)

02 0.236" (BOARD SIDE)


03 0.236" (MATING SIDE)








05 0.237" (BOARD SIDE)






91 0.237" BOARD SIDE

NOTE: 4-40 FEMALE SCREW LOCK IS REMOVABLE

90 0.237" (BOARD SIDE)



NOTE: 90 OPTION FOR 0.093" MAX. BOARD THICKNESS

TOLERANCE: ALL DIMENSIONS ARE ±0.010

Rohs Compliant		UNITS = inch) NOT SC	ALE FROM DRAW	ING		
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	THE PROPERTY OF NorComp AND SHALL NOT	DRAWN: P. JENKINS		NorComp	SCALE: NTS	SHEET OF 3 3	REV 20
	DATE: 09/12/2005		NorComp	DWG NO.	180-YYY-113RYY1		