





2.54±0.15



Technical Data

Material:

- Pin(outer sleeve): Brass,machined CuZn38Pb2
- Plating(outer sleeve):
- Tin plated:2µm/80µ"Ni, 5µm/200µ"Sn
- Gold Plated:2µm/80µ"Ni,Full gold
- Insulator(black): Glass filled thermoplastic polyester
- UL94V-0

Electrical:

- Current rating: 3Amps/contact max.
- Contact resistance: ≤4mΩ/contact
- Insulation resistance: ≥ 1000MΩ at V=100V
- Operating voltage: 60VAC/DC

Mechanical:

- Operating temperatures: Gold Plated:-55°C to+125°C
- Tin plated:-40°C to+105°C

APPROVALS		DATE	TITLE:			
DRAWN	G.M.Chen	2015/7/17	ELECTRONICS CO.,LTD			
CHECKED			Connector			
APPROVALS			PART NO.	MZ254S-11-XX-10		
TOLERANCES ARE		30 ^{±0.15}	±0.30	ANGLE		
		10 ^{±0.10}	±0.20	UNIT: mm		
		5 ^{±0.10}	±0.15	SCALE: 1:1		
				SHEET 1 OF 1		
				PROJ.		
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

