





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/26/04	
A		ADDED ROHS LOGO	12/17/08	BAS



SPECIFICATIONS:
Material:
 Insulator: Hi-temp thermoplastic, rated UL 94V-0
 Insulator color: Black
 Contacts: Brass
Plating:
 Gold Flash over Nickel underplate on Contact area, Tin over Copper underplate on solder tails
Electrical:
 Operating voltage: 250 VAC max
 Current rating: 3 Amps max
 Contact resistance: 20 mohms max
 Insulation resistance: 5000 Mohms min @ 500 VDC
 Dielectric withstanding voltage: 1000 VAC for 1 minute
Temperature Rating:
 Operating temperature: -40°C to +105°C
Environmental:
 Lead free, RoHS compliant.

A = .100 [2.54] X No. of Positions / 2 + .300 [7.62]
 B = .100 [2.54] X No. of Positions / 2 + .212 [5.40]
 C = .100 [2.54] X No. of Spaces

A

A

B

B

C

C

D

D

6

5

4

3

2

1

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED		TITLE	
INCHES	HOLE	ADAM TECH	
.XX ± .10	ØXX ± .015	909 Rahway Avenue, Union, NJ 07083	
.XXX ± .020	ØXXX ± .015	Phone: 908-687-5000 Fax: 908-687-5710	
.XXX ± .015	ØXXX ± .010	BOX HEADER, VERTICAL, SMT	
APPROVALS	DATE	SIZE PART NO.	
DRAWN SS	10/26/04	BHR-XX-VSG-SMT	
CHECKED		SCALE: NTS	REV. A
APPROVED		SHEET 1 OF 1	

