


This document contains proprietary information and such information may not be disclosed to others for any purposes, not used for sales/marketing/procurement purposes without written permission

REV	DESCRIPTION OF REVISION	ECN NO.	BY	DATE	APPROVED
A	Initial Release	—	H.wei	25/08/17	25/08/17





1Electrical

- 1.1 Impedence 50 Ω
- 1.2 Frequency DC-6GHz
- 1.3 Dielectric withstanding voltage 1000V (rms)
- 1.4 Center contact resistance 3M Ω
- 1.5 Outer contact resistance 2M Ω
- 1.6 Insulation Resistance: 5000M Ω min
- 1.7 VSWR ≤ 1.25

Tel: Lee +86-028-85589664  
 Web: www.henglitaitech.com/cn

Notes:  
 1. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE NOTICE AT ANY TIME  
 2. CUSTOMER OUTLINE DRAWING FOR REFERENCE ONLY

DESIGNER : H.wei 25/08/17	TITLE: Cable assembly				
ENGINEER : L.yu 25/08/17	SMA male R/A to SMA male R/A for .141/RG402 Cable Length 100mm				
APPROVED : W.yi 25/08/17		 DIMENSION IN MILLIMETERS (mm)			
TOLERANCES UNLESS OTHERWISE SPECIFIED X ±0.50 .X ±0.20 .XX ±0.10 ANGLES ±1°	PART NO. HL-SMAMW-141-SMAMW-100MM SIZE A4 SCALE N/A SHEET 1/1 REV A				