


HLT-2/8-8S

8-Way Power Divider


Specifications

SN	Parameters	Specifications
1	频率范围 Frequency Range	2000~8000 MHz
2	插入损耗 Insertion Loss	≤ 1.5 dB (Excluding theoretical loss 未含理论损耗 9.0 dB)
3	输入驻波 Input Port VSWR	Typ.1.16 / Max.1.35
4	输出驻波 Output Port VSWR	Typ.1.14 / Max.1.25
5	隔离度 Isolation	Typ.25dB / Min.18dB
6	幅度平衡 Amplitude Balance	±0.4dB
7	相位平衡 Phase Balance	±5°
8	阻抗 Impedance	50 Ohms
9	端口接头 Input/Output Connectors	SMA-Female (Passivated Stainless Steel)
10	承受功率 Power Rating	Splitter 分路器用时 30W; Combiner 合路器用时 2W
11	工作温度 Operation Temperature	-45°C ~ +85°C
12	表面处理 Surface Finishing	Black paint 黑色烤漆
13	外形尺寸 Outline Dimensions	63*108*10 (mm)
14	重量 Weight	160 (g)




Note: Dimensions (mm / [inch]), General tolerance (±0.3)

HenryTech




HenryTech


HenryTech



HenryTech




HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech


HenryTech



HenryTech




HenryTech




HenryTech

HenryTech




HenryTech


HenryTech



HenryTech




HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech


HenryTech



HenryTech




HenryTech




HenryTech

HenryTech



HenryTech

HenryTech




HenryTech

HenryTech




HenryTech


HenryTech



HenryTech




HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech



HenryTech

HenryTech



HenryTech