

# Vibration Monitoring and Machine Protection Systems

1010 East Main Street, League City, TX 77573 Phone:281.334.0766 Fax: 281.334.4255 www.stiweb.com / www.stiwebstore.com

# **CMCP1100HT Series Low Cost Accelerometer with High Temperature Integral Cable**



#### Features:

- Low Cost Compact Accelerometer
- High Temp. FEP Jacketed Cable (200°C)
- 100mV/g ±5%
- 0.32Hz to 10kHz Frequency Response
- Waterproof, Epoxy Encapsulated
- UV and Oil Resistant
- Stainless Steel Case
- 5m, 10m and 20m Stocked Cable Lengths



## **Typical Applications**

Fans, Motors, Pumps, Compressors, Centrifuges, Conveyors, Air Handlers, Gearboxes, Rolls, Dryers, Presses, Cooling, HVAC, Spindles, Machine Tooling, Process Equipment and many more.

#### **Technical Performance**

Mounted Base Resonance: >25 kHz (nominal)

Sensitivity:  $100 \text{mV/g} \pm 5\% \text{ Nominal 80Hz at } 22^{\circ}\text{C}$ 

Frequency Response: 1.5 Hz to 8 kHz  $\pm 10\%$  (90cpm to 480kcpm)

 $0.32 \text{ Hz to } 10 \text{ kHz } \pm 3 \text{dB} (19.2 \text{cpm to } 600 \text{kcpm})$ 

Isolation: Case Isoalted

Measurement Range: ±50 g

Transverse Sensitivity: Less than 5%

#### **Electrical**

Excitation Voltage: 18 to 28 VDC
Electrical Noise: 0.1mg max
Current Range: 2 to 20mA
Bias Voltage: 8-12 Vdc
Settling Time: 2.0 Second
Output Impedance: <100 Ohms max.
Case Isolation: >108 Ohms at 500 Volts

#### **Environmental**

Operating Temperature Range: -65 to 250°F (-54 to 120°C)

Sealing: Epoxy Encapsulated

Maximum Shock: 7,000 g
Approvals: CE Approved

#### Mechanical


Case Material: Stainless Steel
Sensing Element: PZT/Shear
Mounting Torque: 5.9ft. lbs (8Nm)
Weight: 2.5 Oz (70.7 grams)

Cable Jacket: TPE

Cable Length: See Ordering Information

Cable Temperature Rating: 200°C (+392°F) Mounting Thread: 1/4-28 UNF

# **Dimensions and Wiring**



## **Ordering Information:**

CMCP1100HT	-XX	-XX	-XX	Description
	-05			5 Meter (16') Integral Cable
	-10			10 Meter (32') Integral Cable
	-20			20 Meter (64') Integral Cable
		-00		Flying Leads (Bare Wire)
		-01		Female BNC Connector
		-02		Male BNC Connector
			-00	Standard FEP Jacketed Cable

Example Part Number: CMCP1100HT-05-00-00 (5 Meter Cable, Flying Leads, Standard Cable)

## **Similar Products**



M12 Connector CMCP786A-M12



Submersible CMCP786A-IP



Integral Armored Cable CMCP786A-I