


Specifications:  
 Current Rating:3.0A AC,DC  
 Voltage Rating:250V AC,DC  
 Contact Resistance:20mohm Max  
 Insulation Resistance:1000Mohm Min.  
 Withstanding Voltage:1000V AC/minute  
 Operating Temperature Range:-40°C~+85°C

Material And Finish:  
 Insulator:High Temp. Plastic (Nylon 66 UL94V-0)  
 Insulator Color:Beige  
 Contact:Brass  
 Plating:Tin plated



PCB Layout

Dimension:

Circuits	Dim.A	Dim.B	Circuits	Dim.A	Dim.B
2	2.50	7.50	8	17.50	22.50
3	5.00	10.00	9	20.00	25.00
4	7.50	12.50	10	22.50	27.50
5	10.00	15.00	11	25.00	30.00
6	12.50	17.50	12	27.50	32.50
7	15.00	20.00			

RoHS Compliant

				DRAWN:	GENERAL TOLERANCE: .X=±0.20 .XX=±0.15	<h1 style="color: red; margin: 0;">CnC Tech</h1> <p style="margin: 0;">Industrial Cable and Connector Technology</p>	
				CHECKED:			
					SCALE:1:1	,2.5mm,R/A,Tin Plated,M Series	
	17-Nov-2020			APPROVAL:	SHEET: 1 / 1		
REV	DATE	FILE	BY		PROJECTION:	52125-XX-0200-01	