

1 2 3 4 5 6 7

A

A

B

B

C

C

D

D

E

E

F



F

G

G

H

H



**NOTES:**

**MATERIAL**

- 1. Insulator Material: PBT+30%GF(UL94V-0), Grey
- 2. Contact Material : Brass
- 3. Contact Plating : Gold flash/Tin Over Ni
- ④ AHW xxA-0102-T:30u" Au/Tin Over Ni
- AWHW xxA-0202-T:Gold flash/Tin Over Ni
- ⑤ AHW xxA-0302-T:15u" Au/Tin Over Ni

**ELECTRICAL**

- 1. Current Rating : 3AMP
- 2. Withstand Voltage : 500V AC/Minute
- 3. Contact Resistance : 20mΩ max
- 4. Insulation Resistance: 1000MΩ min



**ENVIRONMENTAL**

- 1. Operation Temperature: -40°C to +105°C
- 2. Packing : Tray packing

**Order information:**

xx : 06,08,10,12,14,16,18,20,24  
26,30,34,40,50,60,64

Dimension antitheses list	
NO. Pin	L
6P-8P	4.00
10P-64P	4.40



**RoHS compliant**

Unit: mm



File No.: E198287

Scale	Free					Date	Name	Customer-No.
TOLERANCE	⑤	Add 15u" Au version	02.07.2021	Daniel	Drawn	25.01.2006	Alex	ASSMANN WSW-No. ⑤ AHW xxA-0x02-T
X.X	±0.40	④ Add 30u" Au version	12.12.2013	Winnie	Approved	02.07.2021	Daniel	
X.XX	±0.25	③ Add UL file no.	12.12.2013	Amy				
X.XXX	±0.15	② Update	29.06.2009	Dean				Drawing-No. <b>ASS 2315 CO</b>
DIM	TOL	① Drawn	25.01.2006	Alex				
Angle	±3°	Id.	Modification	Date	Name			rev05
								Sheet 1/1



1 2 3 4 5 6 7