





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/22/08	
A		REDRAWN	10/17/11	
B		ADDED DIM.	10/21/20	AY/NP



Positions: 2, 4, 6, 8, 10, 12, 14, 16, 18, 20, 22, 24
 A = .165 [4.20] X No. of Spaces per row
 B = .165 [4.20] X No. of Positions per row + .055 [1.40]

SPECIFICATIONS:

Material:
 Insulator: Nylon 66, rated UL 94V-0
 Insulator color: Natural
 Electrical:
 Operating voltage: 600 VAC max
 Current rating: / Circuit (See Chart)
 Insulation resistance: 1000 Mohms min @ 500 VDC
 Dielectric withstanding voltage: 1500 VAC for 1 minute
 Temperature Rating:
 Operating temperature: -40°C to +105°C
 Environmental:
 Lead free, RoHS compliant.

WIRE SIZE	CIRCUITS			
	2	4~6	8~10	12~24
18	9 A	8 A	7 A	6 A
20	7 A	6 A	5 A	5 A
22	5 A	4 A	4 A	4 A
24	4 A	3 A	3 A	3 A



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED	
INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010
APPROVALS	
DRAWN	DATE
DY	9/22/08
CHECKED	
APPROVED	



909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE
**WIRE TO WIRE CONNECTOR HOUSING
 FEMALE, 4.2MM PITCH**

SIZE X	PART NO. DMH-XX-V0	REV. B
REF: S00123T	SCALE: NTS	SHEET 1 OF 1