

6

5

4

3





2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/28/04	



SPECIFICATION:

Material:

Insulator: PBT, glass reinforced, rated UL-94V-0

Insulator color: Black

Contacts: Brass

Contact Plating:

Gold Flash over Nickel underplate overall

Electrical:

Current rating: 1 Amps max.

Contact resistance: 20 mohms max

Insulation resistance: 5000 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C TO +105°C

Environmental:

Lead free, RoHS compliant.



A = .100 [2.54] X No. of Positions / 2 + .300 [7.60]

B = .100 [2.54] X No. of Positions / 2 + .200 [5.08]

C = .100 [2.54] X No. of Spaces

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

APPROVALS		DATE
DRAWN	SS	7/28/04
CHECKED		
APPROVED		

TITLE BOX HEADER, RIGHT ANGLE PCB MOUNT, 2 ROW .100 PITCH, GOLD FLASH PLATED		
SIZE X	PART NO. BHR-XX-HUA	REV. -
REF:	SCALE: NTS	SHEET 1 OF 1

6

5

4

3

2

1