

Vibration Monitoring and Machine Protection Systems

1010 East Main Street, League City, TX 77573 Phone:281.334.0766 Fax: 281.334.4255 www.stiweb.com / www.stiwebstore.com

CMCP1100 Series Low Cost Compact Accelerometer with Integral Cable



Features:

- Low Cost Compact Accelerometer
- 100mV/g ±5%
- 0.32Hz to 10kHz Frequency Response
- Waterproof, Epoxy Encapsulated
- Integral TPE Jacketed Cable
- UV and Oil Resistant
- Stainless Steel Case
- 5m, 10m and 20m Stocked Cable Lengths



Typical Applications

Fans, Motors, Pumps, Compressors, Centrifuges, Conveyors, Air Handlers, Gearboxes, Rolls, Dryers, Presses, Cooling, HVAC, Spindles, Machine Tooling, Process Equipment and many more.

Technical Performance

Mounted Base Resonance: >25 kHz (nominal)

Sensitivity: 100mV/g ±5% Nominal 80Hz at 22°C

Frequency Response: 1.5 Hz to 8 kHz $\pm 10\%$ (90cpm to 480kcpm)

0.32 Hz to 10 kHz ±3dB (19.2cpm to 600kcpm)

Isolation: Case Isoalted

Measurement Range: ±50 g

Transverse Sensitivity: Less than 5%

Electrical

Excitation Voltage: 18 to 28 VDC
Electrical Noise: 0.1mg max
Current Range: 2 to 20mA
Bias Voltage: 8-12 Vdc
Settling Time: 2.0 Second
Output Impedance: <100 Ohms max.
Case Isolation: >108 Ohms at 500 Volts

Environmental

Operating Temperature Range: -65 to 185°F (-54 to 85°C)

Sealing: Epoxy Encapsulated

Maximum Shock: 7,000 g
Approvals: CE Approved

Mechanical


Case Material: Stainless Steel
Sensing Element: PZT/Shear
Mounting Torque: 5.9ft. lbs (8Nm)
Weight: 2.5 Oz (70.7 grams)

Cable Jacket: TPE

Cable Length: See Ordering Information

Mounting Thread: 1/4-28 UNF

Dimensions and Wiring



Ordering Information:

CMCP1100	-XX	-XX	-XX	Description
	-05			5 Meter (16') Integral Cable
	-10			10 Meter (32') Integral Cable
	-20			20 Meter (64') Integral Cable
		-00		Flying Leads (Bare Wire)
		-01		Female BNC Connector
		-02		Male BNC Connector
			-00	Standard TPE Cable
			-03	TPE Jacketed Cable with Stainless Steel Braided Armor

Example Part Number: CMCP1100-05-00-00 (5 Meter Cable, Flying Leads, Standard Cable)

Similar Products







Integral Armored Cable CMCP786A-I