

NOTES :

I. DIALIGHT PART NUMBERS: 592-XXXX-8XXSNF.

STORAGE IN ACCORDANCE WITH IPC-A-610.

HOUSING: UL-94-VO SILICONE LENS AND LED: UL-94HB

PROPER LEVEL.


8. FLAMMABILITY RATING

2. ...-302SNF SUFFIX MEANS PARTS ARE SUPPLIED ON A 10 PCS. SAMPLE STRIP

7. THIS ASSEMBLY CONTAINS ELECTROSTATIC DISCHARGE SENSITIVE DEVICES (ESDS).


MAINTAIN ALL PRECAUTIONARY MEASURES DURING ASSEMBLY, HANDLING, AND







SAMPLE STRIP

- \* 10 PCS. SAMPLE STRIP. \* PLACE STRIP IN ALUMINUM BARRIER BAG WITH [1] DESICCANT AND [1] HUMIDITY INDICATOR CARD. \* HEAT SEAL BAG.
- \* PLACE LABEL, APPROPRIATE COLOR DOTS, AND MOISTURE SENSITIVITY LEVEL LABEL ON BAG (SEE TABLE). \* LABEL TO INCLUDE P/N, QTY PER BAG, DATE CODE, REV LEVEL LED LOT NO., LED COLOR, LED BIN INTENSITY FOR BOTH LEDS, - AND "COUNTRÝ OF ORIGIN: MEXICO". - ALUMINUM BARRIER BAG INCLUDES MSL LABEL. -AND "COUNTRY OF ORIGIN: MEXICO"



REEL INDICATES MOISTURE SENSITIVITY LEVEL.





RECOMMENDED RoHS COMPLIANT REFLOW PROFILE


FSCM 833


1501 ROUTE 34 SOUTH


FARMINGDALE, NJ 0772

## OPERATING CHARACTERISTICS AT 25°C AMBIENT - SINGLE COLOR LEDS FORWARD REVERSE LUMINOUS COLOR |INTENSITY| WAVELENGTH |WAVELENGTH| VOLTAGE | CURRENT CURRENT (V) @ 20mA (μA) (mcd) (nm) # DESCRIPTION MIN TYP MAX ΤΥΡ TYP MAX MAX23 GREEN 10 | 566 | 570 | 575 572 2.0 2.4 10 @ V<sub>R</sub>=12 V 24 YELLOW 10 | 580 | 587 | 595 | 586 2.0 | 2.4 | 10 @ Vr=5 V


313SNF SUFFIX MEANS PARTS ARE SUPPLIED ON A 13 INCH REEL, 300 pcs/REEL			
3. FRONT AND REAR TERMINALS [OF EACH LED] OF THE ASSEMBLY TO BE WITHIN .005" COPLANARITY.	ABSOLUTE MAXIMUM RATINGS AT 25°C AMBIENT SINGLE COLOR LEDS	GREEN	Υ
<ul><li>4. STORAGE CONDITIONS FOR TAPED PRODUCT: RE-TAPING MAY BE NECESSARY FOR PRODUCT STORED MORE THAN TWELVE MONTHS.</li><li>5. PIN NUMBERS ARE FOR REFERENCE ONLY , DESIGNATION NON-EXISTENT ON PART.</li></ul>	PEAK FORWARD CURRENT (1/200 DUTY CYCLE, 10µs PULSE WIDTH)	1000	
6. MOISTURE SENSITIVITY LEVEL LABEL WILL BE PLACED ON BAG. CHECK CHART FOR	CONTINUOUS FORWARD CURRENT LINEAR DERATING FROM 60°C,	30	







WITH TERMINAL DIMENSIONS



RECOMMENDED PAD LAYOUT - SINGLE COLOR

