


Specifications:  
 Current rating:3.0 Amps  
 Voltage Rating:250V AC, DC  
 Contact resistance:10mohm Max.  
 Insulation resistance:1,000Mohm min.  
 Withstanding Voltage:1,000V AC For One Minute  
 Operating Temperature Rating:-25°C ~ +85°C

Materials and Finsih  
 Insulator:Nylon 66 (UL94V-0)  
 Insulator Color:White  
 Terminal:Brass  
 Plating:Tin Plated



Dimension:

POS.	Dim.A	Dim.B	POS.	Dim.A	Dim.B
2	2.50	7.50	9	20.00	25.00
3	5.00	10.00	10	22.50	27.50
4	7.50	12.50	11	25.00	30.00
5	10.00	15.00	12	27.50	32.50
6	12.50	17.50			
7	15.00	20.00			
8	17.50	22.50			

RoHS Compliant

				DRAWN:	GENERAL TOLERANCE: .X=±0.20 .XX=±0.15	<b>CnC Tech</b> Industrial Cable and Connector Technology	DESCRIPTION: Wire-To Board Header ,2.5mm,R/A,Tin Plated,J Series	SIZE A4
				CHECKED:	UNIT: MM SCALE:1:1			
				APPROVAL:	SHEET: 1 / 1	PART NO:	51125-XX-0200-01	
REV	DATE	FILE	BY		PROJECTION:			

