





A4				 台普 ROCPCU	COMMON TOLERANCE	UNIT	MM	PROJECTED		PRODUCT NAME:		
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP90801P24BA	
A2						X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1						X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	X	± 0.25					Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission
					ANGULAR	—						



性能参数

1. Insulation resistance: $\geq 1000M\Omega$
绝缘电阻 : $\geq 1000M\Omega$
2. Contact stroke: $1.50mm \pm 0.10$
接触行程 : $1.50mm \pm 0.10$
3. welding temperature: $320\text{ }^\circ\text{C} \pm 20\text{ }^\circ\text{C}$
焊接温度: $320\text{ }^\circ\text{C} \pm 20\text{ }^\circ\text{C}$
4. Welding duration: Less than 3 seconds in duration
焊接时长: Less than 3 seconds in duration
5. Nut assembly torque: 5-14N
螺帽装配力矩: 5-14N
6. Protection level: IP65
防护等级: IP65
7. Explosion prevention level: IK08
防暴等级: IK08
8. Working environment temperature: $-20\text{ }^\circ\text{C} \sim +55\text{ }^\circ\text{C}$
工作环境温度: $-20\text{ }^\circ\text{C} \sim +55\text{ }^\circ\text{C}$
9. LED lamp power consumption: 20m以下
LED灯功耗: 20m以下
10. LED lamp lifespan: 40000h
LED寿命: 40000h
11. LED color: Blue
LED颜色: 蓝色
12. LED foot reverse thrust: $\leq 20N$
LED脚反推扭力: $\leq 20N$

A4				 台普 ROCPCU	COMMON TOLERANCE	UNIT	MM	PROJECTED		PRODUCT NAME:
A3						DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP90801P24BA
A2						DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1						ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION DESCRIPTION	ISSUE		ANGULAR					

NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注
1	luminous zone 发光区	PC 塑料	1	
2	Housing 外壳	Aluminum alloy 铝合金	1	Oxidized/Black 氧化/黑色
3	Oring O型圈	Silica gel 硅胶	1	
4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍
5	Base 基座	PBT	1	
6	LEDpin LED脚	Brass 黄铜	1	Silvering 镀银
7				
8				
9				
10				

材质参数

A4				 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP90801P24BA
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR					