





A4				 <b>台普</b> <b>ROCPCU</b>	<table border="1"> <tr> <th colspan="2">COMMON TOLERANCE</th> </tr> <tr> <td>X.XX</td> <td>± 0.10</td> </tr> <tr> <td>X.X</td> <td>± 0.15</td> </tr> <tr> <td>X</td> <td>± 0.25</td> </tr> <tr> <td>ANGULAR</td> <td>—</td> </tr> </table>	COMMON TOLERANCE		X.XX	± 0.10	X.X	± 0.15	X	± 0.25	ANGULAR	—	UNIT	MM	PROJECTED		PRODUCT NAME:
COMMON TOLERANCE																				
X.XX	± 0.10																			
X.X	± 0.15																			
X	± 0.25																			
ANGULAR	—																			
A3					DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP90801P24WA											
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw											
A1					<b>ROCPCU TECHNOLOGY CO.,LTD</b>															
REV	DATE	REVISION	DESCRIPTION	ISSUE	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission															



性能参数

1. Insulation resistance:  $\geq 1000M\Omega$   
绝缘电阻:  $\geq 1000M\Omega$
2. Contact stroke:  $1.50mm \pm 0.10$   
接触行程:  $1.50mm \pm 0.10$
3. welding temperature:  $320\text{ }^\circ\text{C} \pm 20\text{ }^\circ\text{C}$   
焊接温度:  $320\text{ }^\circ\text{C} \pm 20\text{ }^\circ\text{C}$
4. Welding duration: Less than 3 seconds in duration  
焊接时长: Less than 3 seconds in duration
5. Nut assembly torque: 5-14N  
螺帽装配力矩: 5-14N
6. Protection level: IP65  
防护等级: IP65
7. Explosion prevention level: IK08  
防暴等级: IK08
8. Working environment temperature:  $-20\text{ }^\circ\text{C} \sim +55\text{ }^\circ\text{C}$   
工作环境温度:  $-20\text{ }^\circ\text{C} \sim +55\text{ }^\circ\text{C}$
9. LED lamp power consumption: 20m以下  
LED灯功耗: 20m以下
10. LED lamp lifespan: 40000h  
LED寿命: 40000h
11. LED color: white  
LED颜色: 白色
12. LED foot reverse thrust:  $\leq 20N$   
LED脚反推扭力:  $\leq 20N$

A4				 <b>台普</b> <b>ROCPCU</b>	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3					X.XX	$\pm 0.10$	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP90801P24WA
A2					X.X	$\pm 0.15$	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X	$\pm 0.25$	ROCPCU TECHNOLOGY CO., LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR					

NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注
1	luminous zone 发光区	PC 塑料	1	
2	Housing 外壳	Aluminum alloy 铝合金	1	Oxidized/Black 氧化/黑色
3	Oring O型圈	Silica gel 硅胶	1	
4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍
5	Base 基座	PBT	1	
6	LEDpin LED脚	Brass 黄铜	1	Silvering 镀银
7				
8				
9				
10				

材质参数

A4				 <b>ROCPCU</b>	<table border="1"> <tr> <th colspan="2">COMMON TOLERANCE</th> </tr> <tr> <td>X.XX</td> <td>± 0.10</td> </tr> <tr> <td>X.X</td> <td>± 0.15</td> </tr> <tr> <td>X</td> <td>± 0.25</td> </tr> <tr> <td colspan="2">ANGULAR</td> </tr> </table>	COMMON TOLERANCE		X.XX	± 0.10	X.X	± 0.15	X	± 0.25	ANGULAR		UNIT	MM	PROJECTED		PRODUCT NAME:
COMMON TOLERANCE																				
X.XX	± 0.10																			
X.X	± 0.15																			
X	± 0.25																			
ANGULAR																				
A3				DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP90801P24WA												
A2				DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw												
A1				<b>ROCPCU TECHNOLOGY CO.,LTD</b>																
REV	DATE	REVISION	DESCRIPTION	ISSUE	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission															