



A4				 <b>台普</b> <b>ROCPCU</b>	COMMON TOLERANCE X.XX ± 0.10 X.X ± 0.15 X ± 0.25 ANGULAR —	UNIT	MM	PROJECTED		PRODUCT NAME:	
A3			DRAWN BY			FUYUAN	CHECKED BY	COCO	MODEL NO: TP92227P224RA		
A2			DATE			2019	APPROVAL B	ALEN	Https: www.rocpcu.tw		
A1			<b>ROCPCU TECHNOLOGY CO.,LTD</b>								
REV	DATE	REVISION	DESCRIPTION			ISSUE	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				



性能参数


1. Heating current: Ui: AC250V, Ith: 5A  
发热电流: Ui: AC250V, Ith: 5A
2. Rated current:3A/DC36V  
额定电流:3A/DC36V
3. Power-frequency withstand voltage:2000V1min  
工频耐压:2000V1min
4. Insulation resistance:≥1000MΩ  
绝缘电阻 :≥1000MΩ
5. Contact resistance:≤50mΩ  
接触电阻 :≤50mΩ
6. Pressing stroke:2.80mm ± 0.10  
按压行程:2.80mm ± 0.10
7. Contact stroke:1.50mm±0.10  
接触行程 :1.50mm±0.10
8. Nut assembly torque:5-14N  
螺帽装配力矩:5-14N
9. Protection level:IP67  
防护等级:IP67
10. Explosion prevention level: IK10  
防暴等级: IK10
11. Working environment temperature: -20 °C~+55 °C  
工作环境温度: -20 °C~+55 °C
12. Compression torque: ≤ 3.5N  
按压扭力: ≤3.5N

13. Electrical life: 100000 cycles  
电气寿命: 100000 cycles
14. mechanical: 500000cycles  
机械寿命: 500000cycles
15. Operation method:Self repeating form  
操作方式: 自复式
16. Power-frequency withstand voltage: 2000V/1min  
工频耐压: 2000V/1min
17. LED lamp power consumption: 20m以下  
LED灯功耗: 20m以下
18. LED lamp lifespan: 40000h  
LED寿命: 40000h
19. LED color: Red  
LED颜色: 红色
20. LED Lamp Voltage: 24V  
LED灯电压: 24V
21. NO reverse thrust foot torque: ≤30N  
NO反推脚扭力: ≤30N

连接形式

1. Welding temperature of wire: 320 ± 20 °C  
线材焊接温度: 320±20°C  
Wire welding duration: less than 3 seconds  
线材焊接时长: 时长3秒以下
2. Can be used with dedicated connectors:  
可配专用接插件使用:
  - 2.1 Switch function wire: green (C) blue wire (NO) yellow wire (NC)  
开关功能线材: 绿色(C) 蓝线 (NO) 黄线 (NC)
  - 2.2 LED functional wire: red wire positive pole black wire negative pole LED without distinguishing positive and negative poles  
LED功能线材: 红线正极 黑线负极 LED不分正负极

A4				 <b>台普</b> <b>ROCPCU</b>	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92227P224RA
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	<h1 style="text-align: center;">ROCPCU TECHNOLOGY CO.,LTD</h1>				
REV	DATE	REVISION	DESCRIPTION		ISSUE	X					
					ANGULAR	—					


A	B	C	D	E	F	G
<b>材质参数</b>						
10	luminous zone 发光区	PC 塑胶	1			
9	LEDpin LED引脚	Brass 黄铜	1		Silvering 镀银	
8	Base 底座	PA66	1			
7	Pin 引脚	Brass 黄铜	1		gold-plating 镀金	
6	Contact material 接触材质	silver alloy 银合金	1		Silvering 镀银	
5	LED Base LED基座	PA66	1			
4	Arm nut 固定螺帽	Brass 黄铜	1		nickeling 镀镍	
3	Oring O型圈	Silica gel 硅胶	1			
2	Housing 外壳	Aluminum alloy 铝合金	1		Oxidized/Black 氧化/黑色	
1	Key 按键	Aluminum alloy 铝合金	1		Oxidized/Black 氧化/黑色	
NO 序号	Part name 部件名	Material 材料	QTY 数量		Remark 备注	
A4				UNIT	MM	PROJECTED 
A3				DRAWN BY	FUYUAN	CHECKED BY
A2				DATE	2019	APPROVAL B
A1						ALEN
REV	DATE	REVISION	DESCRIPTION	ISSUE	<b>ROCPU TECHNOLOGY CO.,LTD</b>	
					Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission	

**材质参数**



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92227P224RA
DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
<b>ROCPU TECHNOLOGY CO.,LTD</b>				
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				