


Single color electrical schematic diagram  
单色电气原理图



Installation View  
安装视图

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92506P224RA
DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw

**ROCPU TECHNOLOGY CO., LTD**

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission



性能参数

1. Heating current: Ui: AC250V, Ith: 5A  
发热电流: Ui: AC250V, Ith: 5A
2. Rated current:3A/DC36V  
额定电流:3A/DC36V
3. Power-frequency withstand voltage:2000V1min  
工频耐压:2000V1min
4. Insulation resistance:≥1000MΩ  
绝缘电阻 :≥1000MΩ
5. Contact resistance:≤50mΩ  
接触电阻 :≤50mΩ
6. Pressing stroke:2.50mm ± 0.10  
按压行程:2.50mm ± 0.10
7. Contact stroke:1.50mm±0.10  
接触行程 :1.50mm±0.10
8. welding temperature: 320 °C± 20 °C  
焊接温度: 320 °C± 20 °C
9. Welding duration: Less than 3 seconds in duration  
焊接时长: Less than 3 seconds in duration
10. Nut assembly torque:5-14N  
螺帽装配力矩:5-14N
11. Protection level:IP67  
防护等级:IP67
12. Explosion prevention level: IK10  
防暴等级: IK10



13. Working environment temperature: -20 °C~+55 °C  
工作环境温度: -20 °C~+55 °C
14. Compression torque: ≤ 3.00N  
按压扭力: ≤3.00N
15. Electrical life: 100000 cycles  
电气寿命: 100000 cycles
16. mechanical: 500000cycles  
机械寿命: 500000cycles
17. Operation method:Self repeating form  
操作方式: 自复式
18. LED lamp power consumption: 20m以下  
LED灯功耗: 20m以下
19. LED lamp lifespan: 40000h  
LED寿命: 40000h
20. LED color: Red  
LED颜色: 红色
21. LED Lamp Voltage: 24V  
LED灯电压: 24V
22. NO reverse thrust foot torque: ≤30N  
NO反推脚扭力: ≤30N

连接形式

1. Welding temperature of wire: 320 ± 20 °C  
线材焊接温度: 320±20°C  
Wire welding duration: less than 3 seconds  
线材焊接时长: 时长3秒以下
2. Can be used with dedicated connectors:  
可配专用接插件使用:
  - 2.1 1NO1NC开关功能线材Switch function wire: green (C) blue wire (NO) yellow wire (NC)  
1NO1NC开关功能线材: 绿色(C) 蓝线 (NO) 黄线 (NC)
  - 2.2 2NO2NC switch function wire: green black wire (C), blue black wire (NO), yellow white wire (NC)  
2NO2NC开关功能线材: 绿黑线 (C)、蓝黑线 (NO)、黄白线 (NC)
  - 2.3 LED functional wire: red wire positive pole black wire negative pole LED without distinguishing positive and negative poles  
LED功能线材: 红线正极 黑线负极 LED不分正负极

A4					COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92506P224RA
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw
A1					X	± 0.25	ROCPU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR					

NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注
10	luminous zone 发光区	PC 塑胶	1	
9	LEDpin LED引脚	Brass 黄铜	1	Silvering 镀银
8	Base 底座	PA46	1	
7	Pin 引脚	Brass 黄铜	1	gold-plating 镀金
6	Contact material 接触材质	silver alloy 银合金	1	Silvering 镀银
5	LED Base LED基座	PC 塑胶	1	
4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍
3	Oring O型圈	Silica gel 硅胶	1	
2	Housing 外壳	Aluminum alloy 铝合金	1	Oxidized/Black 氧化/黑色
1	Key 按键	Aluminum alloy 铝合金	1	Oxidized/Black 氧化/黑色

A4				 <b>台普</b> <b>ROCPCU</b>	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92506P224RA	
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw	
A1					X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD					
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR						Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission
	A		B		C		D		E		F	G