



| | | | | | | | | | | | | |
|-----|------|----------|-------------|---------------------|------------------|---------|-----------------------------------|--------|------------|------|------------------------|---|
| A4 | | | | <p>台普 ROCPU</p> | COMMON TOLERANCE | | UNIT | MM | PROJECTED | | PRODUCT NAME: | |
| A3 | | | | | X.XX | ± 0.10 | DRAWN BY | FUYUAN | CHECKED BY | COCO | MODEL NO: TP90802G24OA | |
| A2 | | | | | X.X | ± 0.15 | DATE | 2019 | APPROVAL | B | ALLEN | Https: www.rocpu.tw |
| A1 | | | | | X | ± 0.25 | <h1>ROCPU TECHNOLOGY CO.,LTD</h1> | | | | | |
| REV | DATE | REVISION | DESCRIPTION | | ISSUE | ANGULAR | | | | | | Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission |



性能参数

1. Insulation resistance: $\geq 1000M\Omega$
绝缘电阻 : $\geq 1000M\Omega$
2. Contact stroke: $1.50mm \pm 0.10$
接触行程 : $1.50mm \pm 0.10$
3. welding temperature: $320\text{ }^\circ\text{C} \pm 20\text{ }^\circ\text{C}$
焊接温度: $320\text{ }^\circ\text{C} \pm 20\text{ }^\circ\text{C}$
4. Welding duration: Less than 3 seconds in duration
焊接时长: Less than 3 seconds in duration
5. Nut assembly torque: 5-14N
螺帽装配力矩: 5-14N
6. Protection level: IP65
防护等级: IP65
7. Explosion prevention level: IK08
防暴等级: IK08
8. Working environment temperature: $-20\text{ }^\circ\text{C} \sim +55\text{ }^\circ\text{C}$
工作环境温度: $-20\text{ }^\circ\text{C} \sim +55\text{ }^\circ\text{C}$
9. LED lamp power consumption: 20m以下
LED灯功耗: 20m以下
10. LED lamp lifespan: 40000h
LED寿命: 40000h
11. LED color: Orange
LED颜色: 橙色

| | | | | | | | | | | | |
|-----|------|----------|-------------|---|------------------|------------|---------------------------|--------|------------|---|------------------------|
| A4 | | | |  台普 ROCPCU | COMMON TOLERANCE | | UNIT | MM | PROJECTED |  | PRODUCT NAME: |
| A3 | | | | | X.XX | ± 0.10 | DRAWN BY | FUYUAN | CHECKED BY | COCO | MODEL NO: TP90802G240A |
| A2 | | | | | X.X | ± 0.15 | DATE | 2019 | APPROVAL B | ALEN | Https: www.rocpcu.tw |
| A1 | | | | | X | ± 0.25 | ROCPCU TECHNOLOGY CO.,LTD | | | | |
| REV | DATE | REVISION | DESCRIPTION | | ISSUE | ANGULAR | | | | | |

| NO 序号 | Part name 部件名 | Material 材料 | QTY 数量 | Remark 备注 |
|----------|----------------------|-----------------------|-----------|-------------------------|
| 1 | luminous zone 发光区 | PC 塑料 | 1 | |
| 2 | Housing 外壳 | Aluminum alloy 铝合金 | 1 | Oxidized/Black 氧化/黑色 |
| 3 | Oring O型圈 | Silica gel 硅胶 | 1 | |
| 4 | Arm nut 固定螺帽 | Brass 黄铜 | 1 | nickeling 镀镍 |
| 5 | Base 基座 | PBT | 1 | |
| 6 | LEDpin LED脚 | Brass 黄铜 | 1 | Silvering 镀银 |
| 7 | | | | |
| 8 | | | | |
| 9 | | | | |
| 10 | | | | |

材质参数

| | | | | | | | | | | | |
|-----|------|----------|-------------|---|------------------|---------|----------------------------------|--------|------------|---|------------------------|
| A4 | | | |  台普 ROCPCU | COMMON TOLERANCE | | UNIT | MM | PROJECTED |  | PRODUCT NAME: |
| A3 | | | | | X.XX | ± 0.10 | DRAWN BY | FUYUAN | CHECKED BY | COCO | MODEL NO: TP90802G24OA |
| A2 | | | | | X.X | ± 0.15 | DATE | 2019 | APPROVAL B | ALEN | Https: www.rocpcu.tw |
| A1 | | | | | X | ± 0.25 | ROCPCU TECHNOLOGY CO.,LTD | | | | |
| REV | DATE | REVISION | DESCRIPTION | | ISSUE | ANGULAR | | | | | |