





| | | | | | | | | | | | |
|-----|------|----------|-------------|---|------------------|---------|---------------------------|--------|------------|---|-------------------------|
| A4 | | | |  台普 ROCPCU | COMMON TOLERANCE | | UNIT | MM | PROJECTED |  | PRODUCT NAME: |
| A3 | | | | | X.XX | ± 0.10 | DRAWN BY | FUYUAN | CHECKED BY | COCO | MODEL NO: TP91001P24BAB |
| A2 | | | | | X.X | ± 0.15 | DATE | 2019 | APPROVAL B | ALEN | Https: www.rocpcu.tw |
| A1 | | | | | X | ± 0.25 | ROCPCU TECHNOLOGY CO.,LTD | | | | |
| REV | DATE | REVISION | DESCRIPTION | | ISSUE | ANGULAR | | | | | |
| | | A | B | C | D | E | F | G | | | |

| A | | B | | C | | D | | E | | F | | G | |
|----------|------|----------------------|-------------|---|------------------|---------------------------|--------|------------|-----------|---|---------------|---|--|
| 材质参数 | | | | | | | | | | | | | |
| 10 | | | | | | | | | | | | | |
| 9 | | | | | | | | | | | | | |
| 8 | | | | | | | | | | | | | |
| 7 | | | | | | | | | | | | | |
| 6 | | LEDpin LED脚 | | Brass 黄铜 | | 1 | | | | Silvering 镀银 | | | |
| 5 | | Base 基座 | | PBT | | 1 | | | | | | | |
| 4 | | Arm nut 固定螺帽 | | Brass 黄铜 | | 1 | | | | nickeling 镀镍 | | | |
| 3 | | Oring O型圈 | | Silica gel 硅胶 | | 1 | | | | | | | |
| 2 | | Housing 外壳 | | Aluminum alloy 铝合金 | | 1 | | | | Oxidized/Black 氧化/黑色 | | | |
| 1 | | luminous zone 发光区 | | PC 塑料 | | 1 | | | | | | | |
| NO 序号 | | Part name 部件名 | | Material 材料 | | QTY 数量 | | | | Remark 备注 | | | |
| A4 | | | |  台普 ROCPCU | COMMON TOLERANCE | | UNIT | MM | PROJECTED |  | PRODUCT NAME: | | |
| A3 | | | X.XX | | ± 0.10 | DRAWN BY | FUYUAN | CHECKED BY | COCO | MODEL NO: TP91001P24BAB | | | |
| A2 | | | X.X | | ± 0.15 | DATE | 2019 | APPROVAL B | ALEN | Https: www.rocpcu.tw | | | |
| A1 | | | X | | ± 0.25 | ROCPCU TECHNOLOGY CO.,LTD | | | | | | | |
| REV | DATE | REVISION | DESCRIPTION | | ISSUE | | | | | | | | |
| A | | B | | C | | D | | E | | F | | G | |