





A4				 <b>台普</b> <b>ROCPCU</b>	COMMON TOLERANCE	UNIT	MM	PROJECTED		PRODUCT NAME:		
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91001P24GAB	
A2						X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1						X.X	± 0.15	<b>ROCPCU TECHNOLOGY CO.,LTD</b>				
REV	DATE	REVISION	DESCRIPTION		ISSUE	X	± 0.25					<small>Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission</small>
					ANGULAR	—						



性能参数

1. Insulation resistance:  $\geq 1000M\Omega$   
绝缘电阻 :  $\geq 1000M\Omega$
2. Contact stroke:  $1.50mm \pm 0.10$   
接触行程 :  $1.50mm \pm 0.10$
3. welding temperature:  $320\text{ }^\circ\text{C} \pm 20\text{ }^\circ\text{C}$   
焊接温度:  $320\text{ }^\circ\text{C} \pm 20\text{ }^\circ\text{C}$
4. Welding duration: Less than 3 seconds in duration  
焊接时长: Less than 3 seconds in duration
5. Nut assembly torque: 5-14N  
螺帽装配力矩: 5-14N
6. Protection level: IP65  
防护等级: IP65
7. Explosion prevention level: IK08  
防暴等级: IK08
8. Working environment temperature:  $-20\text{ }^\circ\text{C} \sim +55\text{ }^\circ\text{C}$   
工作环境温度:  $-20\text{ }^\circ\text{C} \sim +55\text{ }^\circ\text{C}$
9. LED lamp power consumption: 20m以下  
LED灯功耗: 20m以下
10. LED lamp lifespan: 40000h  
LED寿命: 40000h
11. LED color: Green  
LED颜色: 绿色

A4				 <b>台普</b> <b>ROCPCU</b>	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3					X.XX	$\pm 0.10$	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91001P24GAB
A2					X.X	$\pm 0.15$	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X	$\pm 0.25$	<b>ROCPCU TECHNOLOGY CO.,LTD</b>				
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR	<small>Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission</small>				

NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注
1	luminous zone 发光区	PC 塑料	1	
2	Housing 外壳	Aluminum alloy 铝合金	1	Oxidized/Black 氧化/黑色
3	Oring O型圈	Silica gel 硅胶	1	
4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍
5	Base 基座	PBT	1	
6	LEDpin LED脚	Brass 黄铜	1	Silvering 镀银
7				
8				
9				
10				

材质参数

A4				 <b>台普</b> <b>ROCPCU</b>	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91001P24GAB
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X	± 0.25	<b>ROCPCU TECHNOLOGY CO.,LTD</b>				
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR					