







REV.	Q'TY	ECN. NO.	APR.	DATE

序号	品名	材质
1	0.5后翻卧式双面接胶芯(H2.0)	LCP UL94V-0 本色
2	0.5后翻卧式双面接端子(H2.0)	铜合金/表面镀金
3	0.5后翻卧式双面接后盖(H2.0)	LCP UL94V-0 黑色
4	0.5后翻卧式双面接焊片(H2.0)	铜合金/表面镀锡


技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等現象。(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena.)
2. 温度范围(Temperature range): -25°C ~ +85°C.
3. 额定电压(Rated voltage): 50V, AC/DC(=等效).
4. 接触电阻(Contact resistance): ≤0.03Ω.
5. 绝缘电阻(Insulation resistance): ≥500MΩ.



Part No	Pin	A	B	C
FPC05-H0.5-4AH2.0	4	1.50	2.52	5.54
FPC05-H0.5-5AH2.0	5	2.00	3.02	6.04
FPC05-H0.5-6AH2.0	6	2.50	3.52	6.54
FPC05-H0.5-7AH2.0	7	3.00	4.02	7.04
FPC05-H0.5-8AH2.0	8	3.50	4.52	7.54
FPC05-H0.5-9AH2.0	9	4.00	5.02	8.04
FPC05-H0.5-10AH2.0	10	4.50	5.52	8.54
FPC05-H0.5-11AH2.0	11	5.00	6.02	9.04
FPC05-H0.5-12AH2.0	12	5.50	6.52	9.54
.....
FPC05-H0.5-60AH2.0	60	(60-1)*0.5	(60+1)*0.5+0.20	(60+7)*0.5+0.04
FPC05-H0.5-80AH2.0	80	(80-1)*0.5	(80+1)*0.5+0.20	(80+7)*0.5+0.04

适用扁平线(Applicable Flat Cable)



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd		
TOLERANCE UNLESS OTHERWISE SPECIFIED				
.X±0.35	X.*±5°	APR. Alex	TITLE: 0.5 Pitch 后翻卧式双面接 H2.0	
.XX±0.25	.X.*±3°	CHK. Jack	DWG NO. FPC05-H0.5-NAH2.0	
.XXX±0.15	.XX.*±1°	DRA. Can	CUSTOMER DRAWING	
SIZE A4	SCALE 1:1	SHEET 1/1	REV. A	