








REV.	Q'TY	ECN. NO.	APR.	DATE

序号	品名	材质
1	0.5插拔卧式上接胶芯(H2.0)	LCP UL94V-0 本色
2	0.5插拔卧式上接端子(H2.0)	铜合金/表面镀锡
3	0.5插拔卧式上接后盖(H2.0)	LCP UL94V-0 黑色
4	0.5插拔卧式上接焊片(H2.0)	铜合金/表面镀锡


技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -25° C~85° C.
3. 额定电压: 50V, AC/DC(等效).
4. 接触电阻: ≤0.03Ω.
5. 绝缘电阻: ≥500MΩ

Part No	Pin	A	B	C	D
FPC02-S0.5-4AH2.0	4	1.50	2.56	7.60	5.20
FPC02-S0.5-5AH2.0	5	2.00	3.06	8.10	
FPC02-S0.5-6AH2.0	6	2.50	3.56	8.60	
FPC02-S0.5-7AH2.0	7	3.00	4.06	9.10	
FPC02-S0.5-8AH2.0	8	3.50	4.56	9.60	
FPC02-S0.5-9AH2.0	9	4.00	5.06	10.10	
FPC02-S0.5-10AH2.0	10	4.50	5.56	10.60	
FPC02-S0.5-11AH2.0	11	5.00	6.06	11.10	
FPC02-S0.5-12AH2.0	12	5.50	6.56	11.60	
.....	
FPC02-S0.5-34AH2.0	34	16.50	17.56	22.60	
FPC02-S0.5-35AH2.0	35	17.00	18.06	23.10	
FPC02-S0.5-36AH2.0	36	17.50	18.56	23.60	
.....	
FPC02-S0.5-60AH2.0	60	(60-1)*0.5	(60+1)*0.5+0.06	(60+1)*0.5+0.1	



适用线路板(PCB LAYOUT)



适用扁平线(Applicable Flat Cable)

DIMENSION IN mm	
TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X±0.35	X.*±5°
.XX±0.25	.X.*±3°
.XXX±0.15	.XX.*±1°

厦门市辛译精密电子有限公司
Xiamen XinYi Xyconn Electronics Co.,Ltd

APR. Alex	TITLE: 0.5 Pitch插拔式上接 H2.0
CHK. Jack	DWG NO. FPC02-S0.5-NAH2.0
DRA. Can	PROJ. CUSTOMER DRAWING
SIZE A4	SCALE 1:1 SHEET 1/1 REV. A