



**SPECIFICATIONS**  
 Rated Current: 3.0AMP  
 Contact Resistance: 20mΩMax  
 Withstand Voltage: 1000V AC/DC  
 Insulation Resistance: 1000MΩMin  
 Operation Temperature: -40°C to +105°C

Contact Material: Copper Alloy  
 Contact Plating: Au or Sn Over Ni  
 Insulator Material: Polyester (UL94V-0)  
 Standard: PA6T  
 Max. Processing Temp: 260°C ± 5°C 5S

**Ordering Information**

**XDM 254 - \* - N - Z - \* - \*\***

No. of Rows 1=Single Row 2=Dual Row	No. of Pins 02-40 Pin	Type Z=直针 W=弯针 S=立端 WS=带端	Length 英寸	Contact Plating C0: Gold Flash G1: 1u" Gold G2: 2u" Gold G3: 3u" Gold G4: 10u" Gold G5: 15u" Gold G6: 30u" Gold S0: Gold Flash/Tin S1: Tin
---	--------------------------	---------------------------------------	--------------	---

			GENERAL TOLERANCE	制图 DRAWING	<b>深圳讯答科技有限公司</b> Shenzhen Xunda Technology Co., Ltd			
			DIM TOL	审核 CHECK				
			X.X ±0.30	批准 APPROVAL	产品名称 TITLE	2.54 单排 直排母 (塑高8.5)	版本 REV.	A
			X.XX ±0.20	比例 SCALE	产品料号 PART NO.	XDM254-1-N-Z-8.5-G0	单位 UNITS	mm
			X.XXX ±0.10	投影 Projection	材料 MATERIAL		页次 SHEET	1/1
1	初版发行	日期	Angle ±3.0°					
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						