




REV.	DATE	DESCRIPTION
NC	01/09/06	INITIAL RELEASE



- NOTE:
1. CRIMPED FERRULE
HEX CRIMP SIZE .429"
 2. CONTACT PIN TO SOLDER

NO.	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	APPROVALS	DATE	PART DESCRIPTION	DWG. NO.	NO.	NC	SIZE	SCALE
8								<p>Amphenol Connex</p> <p>UHF CRIMP JACK (FOR RG-8/U CABLE)</p> <p>182335</p>	182335.DWG	NC	A	NA	
7													
6													
5													
4	FERRULE	COPPER	NICKEL	1									
3	CONTACT PIN	BRASS	GOLD	1									
2	INSULATOR	DELFIN	NATURAL	1									
1	BODY	BRASS	NICKEL	1									
<p>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES AND FOR DECIMAL EQUIVALENT DIM.</p> <p>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLING ARE:</p> <p>A - .005 ± 0.000mm</p> <p>B - .001mm ± 0.000mm</p> <p>C - .001mm ± 0.000mm</p> <p>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR HOLE ARE:</p> <p>.020 - .315 = ± 0.007"</p> <p>.315 - 1.180 = ± 0.015"</p> <p>1.180 - 4.724 = ± 0.020"</p>					<p>CHECKED</p> <p>ISSUED</p> <p>SHEET 1 OF 1</p>		<p>APPROVALS</p> <p>DATE</p> <p>01/09/05</p>						
<p>DESCRIPTION</p>						<p>APPROVALS</p>		<p>DATE</p>		<p>SCALE</p>			