

### XT224 Series : SMID Crystal 2.5x2.0 mm

12.000 - 54.000MHz


## • SPECIFICATION


Model	XT224 Series	
Frequency range	12.000 ~ 54.000 MHz	
Frequency tolerance	±10 , 20 , 30ppm (at 25°C)	
Frequency stability	±10 , 20 , 30ppm (Ref. to 25°C)	
Operation temperature	- 20°C ~ + 70°C Typical	
Storage temperature	- 40°C ~ + 125°C	
Load capacitance	Series, 6pF, 8pF, 9pF,10pF,12pF,15pF,18pF, 20pF or Special requirement.	
Drive Level	10uW (200uW max.)	
Series resistance	See below	
Shunt capacitance	3pF max.	
AGING	±3ppm / Year.	

### • EQUIVALENT SERIES RESISTANCE


Frequancy MHz	Model	ESR
12.000-24.000	Fundmental	150 Ω max.
24.001-30.000	Fundmental	80 Ω max.
30.001-54.000	Fundmental	60 Ω max.

# • DIMENSIONS (mm)







★Bottom View



★Recommended Land Pattern



#### REEL PACKING(mm)



• TAPE SPECIFICATION(mm)

