




Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



SPECIFICATIONS

Rated Current:1.5AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°C to +105°C


Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)



P = With Post

默认 = W/O Post

Ordering Information



			GENREL TOLERANCE		制图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD		
			DIM	TOL	审核 CHECK				
			X. X	±0.30	批准 APPROVAL		产品名称 TITLE		2.00双排 排母 贴片 塑高4.3
			X. XX	±0.20			产品料号 PART NO.		版本 REV.
			X. XXX	±0.10	比例 SCALE		PM200-2-N-S-4.3-G0		单位 UNITS
			Angle	±3.0°	投影 Projection		材料 MATERIAL		页次 SHEET
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE							1/1