



③2.54±0.20




⑤2.54±0.15
⑥0.64±0.05
B±0.20
A-0.25±0.20
④2.54±0.20



①3.0±0.20

L 8.5±0.20

②3.0±0.20



Recommended PCB Layout

NOTE:

MATERIAL

HOUSING: PA6T UL94V-0.

CONTACT: Brass (H65).

CONTACT PLATING: Gold over Nickle.

ELECTRICAL

CURRENT RATING: 3AMP.

DIELECTRIC WITHSTANDING VOLTAGE:1000VAC MIN.

CONTACT RESISTANCE: 20mΩ MAX.

INSULATION RESISTANCE:1000MΩ MIN.

ENVIRONMENTAL

TEMPERATURE RANGE: -40° C TO +105° C.

DIMENSION TABLE

注: 1X40P A尺寸不用减去0.25mm

Circuits	Dimension		Circuits	Dimension		Circuits	Dimension	
	A	B		A	B		A	B
1 X 2	5.08	2.54	1 X 15	38.10	35.56	1 X 28	71.12	68.58
1 X 3	7.62	5.08	1 X 16	40.64	38.10	1 X 29	73.66	71.12
1 X 4	10.16	7.62	1 X 17	43.18	40.64	1 X 30	76.20	73.66
1 X 5	12.70	10.16	1 X 18	45.72	43.18	1 X 31	78.74	76.20
1 X 6	15.24	12.70	1 X 19	48.26	45.72	1 X 32	81.28	78.74
1 X 7	17.78	15.24	1 X 20	50.80	48.26	1 X 33	83.82	81.28
1 X 8	20.32	17.78	1 X 21	53.34	50.80	1 X 34	86.36	83.82
1 X 9	22.86	20.32	1 X 22	55.88	53.34	1 X 35	88.90	86.36
1 X 10	25.40	22.86	1 X 23	58.42	55.88	1 X 36	91.44	88.90
1 X 11	27.94	25.40	1 X 24	60.96	58.42	1 X 37	93.98	91.44
1 X 12	30.48	27.94	1 X 25	63.50	60.96	1 X 38	96.52	93.98
1 X 13	33.02	30.48	1 X 26	66.04	63.50	1 X 39	99.06	96.52
1 X 14	35.56	33.02	1 X 27	68.58	66.04	1 X 40	101.60	99.06

RoHS2.0

本圖紙知識產權及版權由深圳市永丰盈电子有限公司所有,未經書面許可不准擅自傳閱、复制和修改。本公司保留法律追究的权利。

类别	针座	品名	CS-1109-1XXX(L8.5)		
版本	A/0	设计	李文畅	X.X	±0.20
制定部门	工程部	绘制	李文畅	X.XX	±0.10
工程图号	CS-1109	审核	周中湖	X.XXX	±0.05
制定日期	2023/05/09	核准	李增才	X.XXXX	±0.01

材料		单位	mm	SHEET 1 OF 1	
颜色		比例	1:1	修改内容	修改日期
画法		数量			
CST 深圳市永丰盈电子有限公司					
ShenZhenYongFengYing ELECTRONICS CO.,LTD.					
