



Recommended PCB Layout

NOTE:

MATERIAL

HOUSING: PA6T BK UL94V-0

CONTACT: Brass.

CONTACT PLATING: GOLD 1u" OVER Ni 50u" FLASH.

ELECTRICAL

CURRENT RATING: 3AMP.

VOLTAGE RATING: 250VAC/DC.

DIELECTRIC WITHSTANDING VOLTAGE: 500VAC MIN.

CONTACT RESISTANCE: 20mΩMAX.

INSULATION RESISTANCE: 1000MΩMIN.

ENVIRONMENTAL

TEMPERATURE RANGE: -40° C TO +105° C.

DIMENSION TABLE

注: 1\*40P A尺寸不用减去0.2mm

Circuits	Dimension		Circuits	Dimension		Circuits	Dimension	
	A	B		A	B		A	B
2 * 2	4.00	2.00	2 * 15	30.00	28.00	2 * 28	56.00	54.00
2 * 3	6.00	4.00	2 * 16	32.00	30.00	2 * 29	58.00	56.00
2 * 4	8.00	6.00	2 * 17	34.00	32.00	2 * 30	60.00	58.00
2 * 5	10.00	8.00	2 * 18	36.00	34.00	2 * 31	62.00	60.00
2 * 6	12.00	10.00	2 * 19	38.00	36.00	2 * 32	64.00	62.00
2 * 7	14.00	12.00	2 * 20	40.00	38.00	2 * 33	66.00	64.00
2 * 8	16.00	14.00	2 * 21	42.00	40.00	2 * 34	68.00	66.00
2 * 9	18.00	16.00	2 * 22	44.00	42.00	2 * 35	70.00	68.00
2 * 10	20.00	18.00	2 * 23	46.00	44.00	2 * 36	72.00	70.00
2 * 11	22.00	20.00	2 * 24	48.00	46.00	2 * 37	74.00	72.00
2 * 12	24.00	22.00	2 * 25	50.00	48.00	2 * 38	76.00	74.00
2 * 13	26.00	24.00	2 * 26	52.00	50.00	2 * 39	78.00	76.00
2 * 14	28.00	26.00	2 * 27	54.00	52.00	2 * 40	80.00	78.00

RoHS2.0

本圖紙知識產權及版權由深圳市永丰盈电子有限公司所有,未經書面許可不准擅自傳閱、复制和修改。本公司保留法律追究的权利。

类别	针座	品名	CS-1126WS-2*XX (L8.7)		
版本	B/0	设计	李文畅	X.X	±0.20
制定部门	工程部	绘制	李文畅	X.XX	±0.10
工程图号	CST-1126	审核	姚培柱	X.XXX	±0.05
制定日期	2023/04/24	核准	周中湖	X.XXXX	±0.01

材料	PA6T	单位	mm
颜色		比例	1:1
画法		数量	
CST 深圳市永丰盈电子有限公司 ShenZhenYongFengYing ELECTRONICS CO., LTD.			

SHEET 1 OF 1		
	修改内容	修改日期