



General Specification
 Current Rating: 1.5A DC /Contact, 20mA DC for LED signals
 Voltage Rating: 125V AC /Contact, 2.0 volts DC for LED signals
 Operating Environment
 Standard Temperature: -20℃~+70℃
 Industrial Temperature: -40℃~+85℃
 Humidity: 20~70%
 Contact Resistance: ≤30mΩ
 Insulation Resistance: ≥500MΩ
 Dielectric Strength: 500V AC / (50HZ) /Min
 Mating And Unmating Force: 3~20N
 Durability: 750 Cycles Min

Material Specification
 Housing :Thermo-plastic, UL94V-0.
 Contact :Alloy Copper
 Shield :Alloy Copper
 Please refer to the customer drawing when customer has specified

序号	名称	材料	数量	镀层/颜色	备注
3	LED灯	树脂/FE	2	NI/AG	
2	插针	PHOSPHOR BRONZE	4	FU ⁷	
1	塑座	PA46	1	BLACK	

网络插座外形图



温州瑞川电子有限公司
 WEN ZHOU RUI CHUAN ELECTRONIC CO., LTD.

绘图:	吴鹏飞	日期:	2023.4.11
审核:	吴鹏飞	日期:	
核准:	吴鹏飞	日期:	

一般公差	品名:	RCH-56-31 (全塑带灯)		
30~ ±0.25	料号:	5631-4YG00010AB26 (RC02524)		
10~30 ±0.20	型号:	RJ45	图号:	
~10 ±0.15	版本:	单位:mm	比例: 1:1	纸张: A4
角度: ±2°	页面:	1 of 1		

版次	A/0	变更履历	新出版发行
----	-----	------	-------

1	2	3
---	---	---

禁止在图面上任意涂改