



LED lamp, super-bright, blue, rated voltage 24 V AC/DC, Wedge base W2 x 4.6 d,

General technical data		
product designation		LED lamp, super bright
type of light source		LED
color of the light source		blue
socket design		W2 x 4.6d
product component		
• series resistor		No
• diode		No
• lamp transformer		No
• light source		Yes
type of voltage of the operating voltage for actuation		AC/DC
operating voltage		
• at AC		
— at 50 Hz rated value	V	24 ... 24
— at 60 Hz rated value	V	24 ... 24
• at DC rated value	V	24 ... 24
relative positive tolerance of the operating voltage	%	10
relative negative tolerance of the operating voltage	%	-15
consumed current for rated value of supply voltage maximum	mA	10
type of electrical connection		Miscellaneous
fastening method		miscellaneous

Certificates/ approvals		
General Product Approval	Declaration of Conformity	Test Certificates



[Miscellaneous](#)

other

[Confirmation](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SB2908-1BD>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SB2908-1BD>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SB2908-1BD>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SB2908-1BD&lang=en

last modified:

12/23/2020 