


# 3AB Equivalent – 6 x 30mm Miniature Ceramic




## Features

- Available in Fast Acting and Slow Blow Types
- RoHS Compliant



**F-04**



## Specifications

**Rated Voltage:** 125V / 250V

**Breaking Capacity:** 125VAC, 10kA; 250VAC, 200A

**Time Current Characteristics:**

### Fast Acting

% of Ampere Rating	Opening Time
110%	4 hours min.
135%	1 hour max.
200%	120 seconds max.

### Slow Blow

% of Ampere Rating	Opening Time	
	100mA to 3A	4A to 20A
110%	4 hours min.	4 hours min.
135%	1 hour max.	1 hour max.
200%	5 – 120 seconds	12 – 120 seconds

## Ordering Information:

NTE Type No.		Rated Current	Diag No.
Fast Acting	Slow Blow		
	74-6SC100MA	100mA	F-04
74-6FC125MA	74-6SC125MA	125mA	F-04
	74-6SC150MA	150mA	F-04
	74-6SC175MA	175mA	F-04
	74-6SC187MA	187mA	F-04
	74-6SC200MA	200mA	F-04
74-6FC250MA	74-6SC250MA	250mA	F-04
	74-6SC300MA	300mA	F-04
74-6FC375MA	74-6SC375MA	375mA	F-04
	74-6SC400MA	400mA	F-04
74-6FC500MA	74-6SC500MA	500mA	F-04
	74-6SC600MA	600mA	F-04
	74-6SC700MA	700mA	F-04
74-6FC750MA	74-6SC750MA	750mA	F-04
74-6FC1A	74-6SC1A	1.0A	F-04
	74-6SC1.25A	1.25A	F-04
	74-6SC1.5A	1.5A	F-04
	74-6SC1.6A	1.6A	F-04
74-6FC2A	74-6SC2A	2.0A	F-04
	74-6SC2.5A	2.5A	F-04
74-6FC3A	74-6SC3A	3.0A	F-04
74-6FC4A	74-6SC4A	4.0A	F-04
74-6FC5A	74-6SC5A	5.0A	F-04
74-6FC6A		6.0A	F-04
	74-6SC6.25A	6.25A	F-04
74-6FC7A	74-6SC7A	7.0A	F-04
74-6FC8A	74-6SC8A	8.0A	F-04
74-6FC10A	74-6SC10A	10A	F-04
74-6FC12A	74-6SC12A	12A	F-04
74-6FC15A	74-6SC15A	15A	F-04
74-6FC20A	74-6SC20A	20A	F-04
NEW 74-6FC25A		25A	F-04

## Accessories:

Description	NTE Type No.
Fuse Clips	74-FC6
Panel Mount Fuse Holder	74-FH6
In-Line Fuse Holder	74-IFH6