




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

| LOC |     | DIST        |                           | REVISIONS |     |      |  |
|-----|-----|-------------|---------------------------|-----------|-----|------|--|
| P   | LTR | DESCRIPTION |                           | DATE      | DWN | APVD |  |
| AD  | 00  | P3          | REVISED PER ECO-12-010411 | 05JUN12   | KH  | MM   |  |



RECOMMENDED P.C. BD. LAYOUT



SECTION Z-Z

| FINISH   | B     | A     | NO OF POSN | PART NUMBER |
|----------|-------|-------|------------|-------------|
| OBSOLETE | .500  | .858  | 12         | 6-534972-5  |
| OBSOLETE | .700  | 1.058 | 16         | 6-534972-4  |
| OBSOLETE | 7.900 | 8.258 | 160        | 6-534972-3  |
| OBSOLETE | 6.900 | 7.258 | 140        | 6-534972-2  |
| OBSOLETE | 6.400 | 6.758 | 130        | 6-534972-1  |
| OBSOLETE | 5.900 | 6.258 | 120        | 6-534972-0  |
| OBSOLETE | 5.100 | 5.458 | 104        | 5-534972-9  |
| OBSOLETE | 4.900 | 5.258 | 100        | 5-534972-8  |
| OBSOLETE | 4.400 | 4.758 | 90         | 5-534972-7  |
| OBSOLETE | 3.900 | 4.258 | 80         | 5-534972-6  |
| OBSOLETE | 3.400 | 3.758 | 70         | 5-534972-5  |
| OBSOLETE | 2.900 | 3.258 | 60         | 5-534972-4  |
| OBSOLETE | 2.400 | 2.758 | 50         | 5-534972-3  |
| OBSOLETE | 1.900 | 2.258 | 40         | 5-534972-2  |
| OBSOLETE | 1.400 | 1.758 | 30         | 5-534972-1  |
| OBSOLETE | .500  | .858  | 12         | 1-534972-5  |
| OBSOLETE | .700  | 1.058 | 16         | 1-534972-4  |
| OBSOLETE | 7.900 | 8.258 | 160        | 1-534972-3  |
| OBSOLETE | 6.900 | 7.258 | 140        | 1-534972-2  |
| OBSOLETE | 6.400 | 6.758 | 130        | 1-534972-1  |
| OBSOLETE | 5.900 | 6.258 | 120        | 1-534972-0  |
| OBSOLETE | 5.100 | 5.458 | 104        | 534972-9    |
| OBSOLETE | 4.900 | 5.258 | 100        | 534972-8    |
| OBSOLETE | 4.400 | 4.758 | 90         | 534972-7    |
| OBSOLETE | 3.900 | 4.258 | 80         | 534972-6    |
| OBSOLETE | 3.400 | 3.758 | 70         | 534972-5    |
| OBSOLETE | 2.900 | 3.258 | 60         | 534972-4    |
| OBSOLETE | 2.400 | 2.758 | 50         | 534972-3    |
| OBSOLETE | 1.900 | 2.258 | 40         | 534972-2    |
| OBSOLETE | 1.400 | 1.758 | 30         | 534972-1    |

- 1 HSG. POLYPHENYLENE SULFIDE.
- 2 CONTACT: PHOS BRONZE.
- 3 DUPLEX PLATED: .000030 GOLD ON CONTACT AREA ONLY, .000050-.000100 BRIGHT TIN-LEAD ON SOLDER TINES ALL OVER .000050 NICKEL ENTIRE CONTACT.
- 4 "AMP", "CSA", DATE CODE, AND PART NUMBER MARKED WITH .062±.015 HIGH CHARACTERS. THE ORDER AND LOCATION IS OPTIONAL.
- 5 POINT OF MEASUREMENT FOR PLATING THICKNESS INSIDE BEAMS.
- 6 TOLERANCE NON-CUMULATIVE.
- 7 THESE DIMENSIONS PERTAIN TO CAVITY CENTERLINES NOT THE CONTACT LOCATIONS.
- 8 OBSOLETE PART NUMBER.
- 9 PRELIMINARY PART - NOT RELEASED FOR PRODUCTION
- 10 DUPLEX PLATED: .000030 GOLD ON CONTACT AREA ONLY, .000050-.000100 MATTE TIN ON SOLDER TINES ALL OVER .000050 NICKEL ENTIRE CONTACT.
- 11 ROHS 2002/95/EC COMPLIANT.
- 12 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.

|      |           |         |
|------|-----------|---------|
| DWN  | M. SMITH  | 6-25-87 |
| CHK  | D. SARVER | 7-8-87  |
| APVD | D. SARVER | 7-8-87  |

TE Connectivity

RECEPTACLE ASSY, VERTICAL  
 MT, MOD II, .100 x .100CL  
 WITH MTG EARS, SHORT-POINT

|                  |       |           |       |            |          |
|------------------|-------|-----------|-------|------------|----------|
| SIZE             | A2    | CAGE CODE | 00779 | DRAWING NO | C=534972 |
| WEIGHT           | -     | SCALE     | 4:1   | SHEET      | 1 of 1   |
| CUSTOMER DRAWING | SCALE |           | 4:1   | SHEET      | 1 of 1   |

RESTRICTED TO