SIEMENS

Data sheet

6GK5898-1CV00-4AA0

product type designation

IWLAN angle adapter SMA/SMA male/female

Elbow adapter SMA/SMA male/female



electrical data	
number of electrical connections	2
type of electrical connection	SMA male / SMA female
transmission frequency	0 6 GHz
impedance	50 Ω
ambient conditions	
ambient temperature	
 during operation 	-20 +80 °C
 during storage 	-20 +80 °C
during transport	-20 +80 °C
protection class IP	IP61
design, dimensions and weights	
width	17 mm
height	15 mm
standards, specifications, approvals	
certificate of suitability	
 RoHS conformity 	Yes
further information / internet-Links	
Internet-Link	
 to website: TIA Selection Tool 	http://www.siemens.com/tia-selection-tool
 to web page: selection aid TIA Selection Tool 	http://www.siemens.com/snst
• to the website: IWLAN	http://www.siemens.com/iwlan
 to website: Industrial communication 	http://www.siemens.com/simatic-net
 to website: Industry Mall 	https://mall.industry.siemens.com
to website: Information and Download Center	http://www.siemens.com/industry/infocenter
to website: Image database	http://automation.siemens.com/bilddb
to website: CAx-Download-Manager	http://www.siemens.com/cax
 to website: Industry Online Support 	https://support.industry.siemens.com

last modified:

12/18/2020