
т	۵	п	m	0







LAYOUT SHOWN AS

Keying Shown as example

L

С

CHARACTERISTICS

ယ

 \sim

-Mass

BASIC SERIES:

SHELL SIZE : 13

Н

SHELL TYPE : Square Flange Receptacle

CONTACT TYPE : Standard Crimp Contact

PLATING : J = Olive drab Cadmium

-Standard : Based on MIL-DTL-38999 Series III

ł	-Shell Material	: Composite		
	-Shell Plating	: Olive drab Cadmium		
	-Insulator	: Thermoplastic		
	-Contacts	: Copper Alloy		
	-Seals & Grommet	: Silicon Elastomer		
	-Contact Plating	: Gold over copper Alloy 0.8µm minimum		
	-Durability	: 500 Mating cycles		
	-Delivered without Souriau contacts			
	-Temperature Range	65℃ to +175℃		
	-Salt Spray	: 2000 hours		

: 12.9 g ± 10%

8D 0

G

13

J

08

Ρ

F

Connector dimension			
Dim	Nominal		
Р	3.25±0.2		
PP	4.93±0.2		
R1	23.01		
R2	20.62		
S	28.6±0.3		
V'	19.5+1.4/-0		
W'	2.1/3.65		
Ζ'	32 Max		
VV THREAD	M18x1-6g		

Delivered W/O Contacts


CONTACT LAYOUT : 13-08

CONTACT TYPE : PIN(500 Matings)

Е

ORIENTATION : C

SOURIAU shall not be liable for a due to a use of the Products the Specifications issued by either (professional recommend



	Φ		A			
					4	
					3	
IS EXA	MPLE					
whic er of t	non-conformit h does not co he Parties or t n, technical n	mply with by a third part	ty			
intry R	Jurisdiction & Control List Not Listed				2	
310	BJ08PCL					
				MOD N°		
		CUSTOME	R DRAWING			
ite	te Receptacle 8D series					
ar	NPRDS / PROJECT 859					
.COM This document is the property of SOURIAU it must not be reproduced or communicated without permission					1	
	DRG N°			SHEET	-	
J08	PCL-C		Λ	1/2	J	
	В		А			

	T	۵	н Г	m	U	0	
		Contact Layout					Panel Cutout
4	х.	$ \begin{pmatrix} & & & & \\ & & & & \\ & & & \\ & & & & \\ & & & \\ &$			Λ	SQUARE FLANGE RECEPTACLE (TYPE REAR MOUNTING	0)
	Con posi II A E C C C C C C C C C C C C C C C C C C	Uion D X-axis (mm) Y-axis (mm) A +.065 (1.65) +.157 (3.99) B +.170 (4.32) +.000 (0.00) C +.120 (3.05) 120 (3.05) D .000 (0.00) 170 (4.32) E 120 (3.05) 120 (3.05) F 170 (4.32) +.000 (0.00) S 065 (1.65) +.157 (3.99)			₩ ₩		
သ		mber of Size Service Contact Supersedes ntacts contacts rating location 8 8 20 I All MS20051-8				<u>s</u>	Dim ØA ØAA R1 ØT
						SOURIAU shall not due to a use of t the Specifications issu (professiona	he Products whi
2						PN	Country FR 8D013J(
					A 14-10-20 ISS DATE Designed By:	16 First Release Latest modification - Date:	
_					TITLE SCALE NA		Composite General linear Tolerances: ±
					SOURIA		
					FORMAT A3		OURIAU 8D013J0
	Н	G	F	E	D	С	

